

ABB Motors and Generators		Technical Data Sheet - DOL			
		Project _____		Location _____	
Department/Author _____		Customer name _____		Customer ref. _____	
Our ref. _____		Rev/Changed by _____		Date of issue _____	
				Saving ident _____	
				Pages 1(3)	


No.	Definition	Data	Unit	Remarks
1	Product	TEFC, 3-phase, squirrel cage induction motor		
2	Product code	MM28754-PP (3GBP282210-ADG+332+333+531)		
3	Type/Frame	M3BP 280 SMA 4		
4	Mounting	IM1001, B3(foot)		
5	Rated output P _N	75	kW	
6	Service factor	1		
7	Type of duty	S1(IEC) 100%		
8	Rated voltage U _N	400	VD	± 5 % (IEC 60034-1)
9	Rated frequency f _N	50	Hz	± 2 % (IEC 60034-1)
10	Rated speed n _N	1484	r/min	
11	Rated current I _N	134	A	
12	No-load current	46	A	
13	Starting current I _s /I _N	6.9		Fullfilled IEC 60034-12 design N,H
14	Nominal torque T _N	483	Nm	
15	Locked rotor torque T _S /T _N	2.5		
16	Maximum torque T _{max} /T _N	2.8		
17	Minimum torque T _{min} /T _N	2.2		
18	Speed at minimum torque	1200	r/min	
19	Load characteristics (IEC 60034-2-1:2007)	Load %	Current A	Efficiency %
20	PLL determined from residual loss	100	134	94.5 / IE2
21		75	104	94.5
22		50	78.9	93.9
23		Start	929	0.42
24	Maximum starting time from hot	18	s	
25	Maximum starting time from cold	32	s	
26	Insulation class / Temperature class	F / B		
27	Ambient temperature	40	°C	
28	Altitude	1000	m.a.s.l.	
29	Enclosure	IP55		
30	Cooling system	IC411 self ventilated		
31	Bearing DE/NDE	6316/C3 - 6316/C3		
32	Type of Grease	Lithium based		
33	Sound pressure level (LP dB(A) 1m)	68	dB(A)	at load
34	Moment of inertia J = ¼ GD2	1.25	kg-m2	
35	Balancing	Half Key		
36	Vibration class	Grade A		
37	Position of terminal box	Top		
38	Terminal box entries; no, dimens.	2xM63x1.5 + 2xM20x1.5		
39	Number of power terminals	6		
40	Direction of rotation	CW or CCW		
41	Total weight of motor	625	kg	
42				

Variant Codes / Definition

332 = Baldor catalog number
333 = Not for use in the USA
531 = Sea freight packaging

Remarks:

Data based on situation 2/25/2013
 All data subject to tolerances in accordance with IEC
 Guaranteed values on request






ABB Motors and Generators		Technical Data Sheet - DOL				
		Project		Location		
Department/Author		Customer name		Customer ref.		Item name
Our ref.		Rev/Changed by	Date of issue	Saving ident		Pages 1(3)


No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	MM28754-PP (3GBP282210-ADG+332+333+531)			
3	Type/Frame	M3BP 280 SMA 4			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	75	kW		
6	Service factor	1			
7	Type of duty	S1(IEC) 100%			
8	Rated voltage U _N	415	VD	± 5 % (IEC 60034-1)	
9	Rated frequency f _N	50	Hz	± 2 % (IEC 60034-1)	
10	Rated speed n _N	1486	r/min		
11	Rated current I _N	131	A		
12	No-load current	50	A		
13	Starting current I _s /I _N	7.3		Fullfilled IEC 60034-12 design N,H	
14	Nominal torque T _N	482	Nm		
15	Locked rotor torque T _S /T _N	2.7			
16	Maximum torque T _{max} /T _N	3			
17	Minimum torque T _{min} /T _N	2.3			
18	Speed at minimum torque	1200	r/min		
19	Load characteristics (IEC 60034-2-1:2007)	Load %	Current A	Efficiency %	Power factor
20	PLL determined from residual loss	100	131	94.5 / IE2	0.84
21		75	103	94.5	0.8
22		50	78.4	93.7	0.71
23		Start	959		0.42
24	Maximum starting time from hot	18	s		
25	Maximum starting time from cold	36	s		
26	Insulation class / Temperature class	F / B			
27	Ambient temperature	40	°C		
28	Altitude	1000	m.a.s.l.		
29	Enclosure	IP55			
30	Cooling system	IC411 self ventilated			
31	Bearing DE/NDE	6316/C3 - 6316/C3			
32	Type of Grease	Lithium based			
33	Sound pressure level (LP dB(A) 1m)	68	dB(A)	at load	
34	Moment of inertia J = ¼ GD2	1.25	kg-m2		
35	Balancing	Half Key			
36	Vibration class	Grade A			
37	Position of terminal box	Top			
38	Terminal box entries; no, dimens.	2xM63x1.5 + 2xM20x1.5			
39	Number of power terminals	6			
40	Direction of rotation	CW or CCW			
41	Total weight of motor	625	kg		
42					

Variant Codes / Definition

332 = Baldor catalog number
333 = Not for use in the USA
531 = Sea freight packaging

Remarks:

Data based on situation 2/25/2013
All data subject to tolerances in accordance with IEC
Guaranteed values on request






ABB Motors and Generators		Technical Data Sheet - DOL				
		Project		Location		
Department/Author		Customer name		Customer ref.		Item name
Our ref.		Rev/Changed by	Date of issue	Saving ident		Pages 1(3)

No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	MM28754-PP (3GBP282210-ADG+332+333+531)			
3	Type/Frame	M3BP 280 SMA 4			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	75	kW		
6	Service factor	1			
7	Type of duty	S1(IEC) 100%			
8	Rated voltage U _N	690	VY	± 5 % (IEC 60034-1)	
9	Rated frequency f _N	50	Hz	± 2 % (IEC 60034-1)	
10	Rated speed n _N	1484	r/min		
11	Rated current I _N	78.1	A		
12	No-load current	27	A		
13	Starting current I _s /I _N	6.9		Fullfilled IEC 60034-12 design N,H	
14	Nominal torque T _N	483	Nm		
15	Locked rotor torque T _S /T _N	2.5			
16	Maximum torque T _{max} /T _N	2.8			
17	Minimum torque T _{min} /T _N	2.2			
18	Speed at minimum torque	1200	r/min		
19	Load characteristics (IEC 60034-2-1:2007)	Load %	Current A	Efficiency %	Power factor
20	PLL determined from residual loss	100	78.1	94.5 / IE2	0.85
21		75	60.7	94.5	0.82
22		50	45.7	93.9	0.73
23		Start	539		0.42
24	Maximum starting time from hot	18	s		
25	Maximum starting time from cold	32	s		
26	Insulation class / Temperature class	F / B			
27	Ambient temperature	40	°C		
28	Altitude	1000	m.a.s.l.		
29	Enclosure	IP55			
30	Cooling system	IC411 self ventilated			
31	Bearing DE/NDE	6316/C3 - 6316/C3			
32	Type of Grease	Lithium based			
33	Sound pressure level (LP dB(A) 1m)	68	dB(A)	at load	
34	Moment of inertia J = ¼ GD2	1.25	kg-m2		
35	Balancing	Half Key			
36	Vibration class	Grade A			
37	Position of terminal box	Top			
38	Terminal box entries; no, dimens.	2xM63x1.5 + 2xM20x1.5			
39	Number of power terminals	6			
40	Direction of rotation	CW or CCW			
41	Total weight of motor	625	kg		
42					

Variant Codes / Definition

332 = Baldor catalog number
333 = Not for use in the USA
531 = Sea freight packaging

Remarks:

Data based on situation 2/25/2013
All data subject to tolerances in accordance with IEC
Guaranteed values on request

