

ABB BALDOR RELIANCE III

Customer information packet

M3564

.5HP, 1735RPM, 3PH, 60HZ, 66, 3511M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	66
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.420 A @ 208.0 V 2.240 A @ 230.0 V 1.120 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	72.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	W
Type	AC
Mech. spec.	35E029
Base	
Status	NLA/A
Elec. spec.	35WGP864
Layout	35LYE029
Eff. date	01-16-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-09-2008

Heater Indicator	No Heater
High Voltage Full Load Amps	1.1 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	M
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3512M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.62 IN
Power Factor	58
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.750 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1740 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor



Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L											
CAT.NO.											
SPEC.	35E029P864										
HP	.5										
VOLTS	208-230/460										
AMP	2.42-2.24/1.12										
RPM	1740										
FRAME	66		HZ		60		PH		3		
SER.F.	1.25	CODE		M	DES	B	CLASS		F		
NEMA-NOM-EFF	72	PF		58							
RATING	40C AMB-CONT										
CC											
DE	6205		ODE		6203						
ENCL	TEFC	SN									
	SFA 2.6-2.4/1.2										

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data

Record # 28087

Typical performance - not guaranteed values

Winding: 35WGP864-R001			Type: 3512M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		.5	Full Load Torque		1.52 LB-FT		
Volts		208-230/460	Start Configuration		direct on line		
Full Load Amps		2.42-2.24/1.12	Breakdown Torque		7.46 LB-FT		
R.P.M.		1740	Pull-up Torque		4.83 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		5.45 LB-FT	
NEMA Design Code		B	KVA Code		M		
Service Factor (S.F.)		1.25	Starting Current		6.6 A		
NEMA Nom. Eff.		72	Power Factor		58		
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		41°C
S.F. Amps					Temp. Rise @ S.F. Load		47°C
					Locked-rotor Power Factor		80.2
					Rotor inertia		0.0709 LB-FT2

Load Characteristics 460 V, 60 Hz, 0.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	27	39	50	61	69	75	66
Efficiency	47.1	62.6	70.3	73.8	75.6	75.6	73.8
Speed	1786	1773	1759	1745	1729	1708	1726
Line amperes	0.926	0.953	1	1.06	1.14	1.28	1.2

ABB Motors and Mechanical Inc.

WINDING # 35WGP864

Typical performance - not guaranteed values.

0.5 HP 3 PH 60 HZ 1740 RPM 460 V 3512M

TORQUES (LB-FT) : PO=7.46 PU=4.83 LR=5.45 LRA=6.6



