

ABB BALDOR RELIANCE III

Customer information packet

M3613T-57

5HP, 2860RPM, 3PH, 50HZ, 184T, 3632M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	184T
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	3000 RPM @ 50 HZ
Voltage @ Frequency	230.0 V @ 50 HZ 400.0 V @ 50 HZ
Agency Approvals	CSA CE UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	11.400 A @ 230.0 V 6.600 A @ 400.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	P
Type	AC
Mech. spec.	36A001
Base	
Status	NLA/A
Elec. spec.	36WGS809
Layout	36LYA001
Eff. date	10-28-2016
CD Diagram	CD0022
Poles	02
Leads	6#16
Proprietary	False
Created date	09-20-2011

High Voltage Full Load Amps	6.6 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3632M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	16.54 IN
Power Factor	95
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	2860 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP2717L									
CAT NO	M3613T-57								
SPEC.	36A001S809H1								
HP	5					PH	3		
VOLTS	230/400								
AMP	11.4/6.6								
FRAME	184T		HZ	50		I.P.	54		
SER.F.	1.15	CODE	K	DES	B	CL	F		
NEMA-NOM-EFF	86					% (100%)			
PF	95								
RATING	40C AMB-CONT				CC				
DE BRG	6206		ODE	6205					
ENCL	TEFC	SN							
BLANK	IE2-86.0(75%)84.5(50%)								

AC Induction Motor Performance Data

Record # 35195

Typical performance - not guaranteed values

Winding: 36WGS809-R001			Type: 3632M		Enclosure: TEFC		
Nameplate Data			400 V, 50 Hz: High Voltage Connection				
Rated Output (HP)		5	Full Load Torque		9.25 LB-FT		
Volts		230/400	Start Configuration		direct on line		
Full Load Amps		11.4/6.6	Breakdown Torque		42.9 LB-FT		
R.P.M.		2860	Pull-up Torque		27.4 LB-FT		
Hz	50	Phase	3	Locked-rotor Torque		31.1 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		59.8 A
Service Factor (S.F.)		1.15	No-load Current		1.84 A		
NEMA Nom. Eff.		86	Power Factor	95	Line-line Res. @ 25°C		2.27 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		78°C
S.F. Amps					Temp. Rise @ S.F. Load		97°C
					Locked-rotor Power Factor		54
					Rotor inertia		0.143 LB-FT2

Load Characteristics 400 V, 50 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	73	90	94	95	94	93	94
Efficiency	80.9	84.5	86.3	86.4	84.8	82.2	85.4
Speed	2969	2937	2900	2860	2816	2768	2834
Line amperes	2.36	3.56	5.03	6.6	8.39	10.3	7.67


ABB Motors and Mechanical Inc.

WINDING # 36WGS809


Typical performance - not guaranteed values.

5 HP 3 PH 50 HZ 2860 RPM 400 V 3632M


TORQUES (LB-FT) : PO=42.9 PU=27.4 LR=31.1 LRA=59.8




CD0022



LOW VOLTAGE
(1D)



HIGH VOLTAGE
(1Y)



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: F	BY: JLP	REVISED: 01/21/99 3:54	TDR: 0171435
CD0022		FILE: AAA00005144	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 6 LEADS, DELTA/WYE CONNECTION

CD0022