ABB BALDOR RELIANCE

Customer information packet

M7034T

1.5//1HP, 1755//1460RPM, 3PH, 60//50HZ, 145T
Class -
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 7:42:37 AM

Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Steel
Frequency	50.00 Hz
	60.00 Hz
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
	1.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
	1800 RPM @ 60 HZ
Voltage @ Frequency	380.0 V @ 50 HZ
	460.0 V @ 60 HZ
	190.0 V @ 50 HZ
	230.0 V @ 60 HZ
Agency Approvals	UL
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.100 A @ 380.0 V
	2.400 A @ 460.0 V
	4.200 A @ 190.0 V
	4.800 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %

Part Detail

Revision	G
Type	AC
Mech. spec.	35E362
Base	
Status	NLA/A
Elec. spec.	35WGZ541
Layout	35LYE362
Eff. date	09-15-2009
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	12-11-2006

Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	2.1 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	M
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3521M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.23 IN
Power Factor	70
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1460 rpm

	1755 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1426XP								
NO.		**CC**	010A					
SER.								
SPEC.	35E362Z541H1							
CAT.NO.	M7034T							
HP	1.5//1			**T. CODE**	T3C			
VOLTS	230/460//190/380							
AMPS	4.8/2.4//4.2/2.1							
RPM	1755//1460							
HZ	60//50	**PH**	3	**CL**	B			
SER.F.	1.00	**DES**	B	**CODE**	M			
RATING	40C AMB-CONT							
FRAME	145T	**NEMA-NOM-EFF**		84		**PF**	70	

AC Induction Motor Performance Data
Record # 28529
Typical performance - not guaranteed values


Winding: 35WGZ541-R004	**Type:** 3522M	**Enclosure:** XPFC


Nameplate Data			
Rated Output (HP)			1.5//1
Volts			230/460//190/380
Full Load Amps			4.8/2.4//4.2/2.1
R.P.M.			1755//1460
Hz	60//50	**Phase**	3
NEMA Design Code	B	**KVA Code**	M
Service Factor (S.F.)			1
NEMA Nom. Eff.	84	**Power Factor**	70
Rating - Duty			40C AMB-CONT

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	4.42 LB-FT
Start Configuration	direct on line
Breakdown Torque	19.8 LB-FT
Pull-up Torque	10.65 LB-FT
Locked-rotor Torque	14 LB-FT
Starting Current	19.38 A
No-load Current	1.59 A
Line-line Res. @ 25ºC	9.72 Ω
Temp. Rise @ Rated Load	55°C
Locked-rotor Power Factor	53.6
Rotor inertia	0.13 LB-FT2


Load Characteristics 460 V, 60 Hz, 1.5 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	30	48	62	70	77	80
Efficiency	68.5	79.3	83.4	84.3	84.2	83.1
Speed	1792	1783	1773	1762	1751	1737
Line amperes	1.64	1.8	2.04	2.35	2.7	3.11


ABB Motors and Mechanical Inc.
WINDING # 35WGZ541
1.5 HP 3 PH 60 HZ 1762 RPM 460 V 3522M
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=19.8 PU=10.65 LR=14 LRA=19.38
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (1.5 HP)
11/19/2026 ACPERF, record # 28529


35LYE362
510-520 = 14.34
521-528 = 15.21
529-535 = 16.09
536 - 546 = 17.46
2.46
2.25
.19 KEY
1.38 LONG
Ø7.19
X-PROOF NAMEPLATE
BALDOR
PT. NO. 35CB3500
Ø .8750
.8745
4.72
4.00
2.25
5.00
.50
5.94
6 HOLES
.34 WIDE
6.67
6.92
7.08
3.50
3.44
LEAD HOLE
.75 N.P.T.
2.75
2.75
5.33
3.25
6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD TO SOLIDWORKS
REV: K
VERSION: 04
REVISED: 02:37:58 08/29/2019
TDR: 000001117187
MODEL NO. 35LYE362
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
STD HORZ NEMA 143-5T XPFC X35M CL-I GP-D CL-II GP-F&G
35LYE362

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS