


ABB Motors and Generators		Technical Data Sheet - DOL				
		Project		Location		
Department/Author		Customer name		Customer ref.		Item name
Our ref.		Rev/Changed by	Date of issue	Saving ident		Pages 1(3)

No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	MM09152-PP (3GBP091322-ASB+332+333)			
3	Type/Frame	M3BP 90 SLB 2			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	1.5	kW		
6	Service factor	1			
7	Type of duty	S1(IEC) 100%			
8	Rated voltage U _N	230	VD	± 5 % (IEC 60034-1)	
9	Rated frequency f _N	50	Hz	± 2 % (IEC 60034-1)	
10	Rated speed n _N	2900	r/min		
11	Rated current I _N	5.3	A		
12	No-load current	1.83	A		
13	Starting current I _s /I _N	7.5		Fullfilled IEC 60034-12 design N,H	
14	Nominal torque T _N	4.9	Nm		
15	Locked rotor torque T _S /T _N	2.5			
16	Maximum torque T _{max} /T _N	2.6			
17	Minimum torque T _{min} /T _N	2			
18	Speed at minimum torque	690	r/min		
19	Load characteristics (IEC 60034-2-1:2007)	Load %	Current A	Efficiency %	Power factor
20	PLL determined from residual loss	100	5.3	82.2 / IE2	0.86
21		75	4	84.1	0.83
22		50	2.9	82.7	0.77
23		Start	39		0.62
24	Maximum starting time from hot	10	s		
25	Maximum starting time from cold	18	s		
26	Insulation class / Temperature class	F / B			
27	Ambient temperature	40	°C		
28	Altitude	1000	m.a.s.l.		
29	Enclosure	IP55			
30	Cooling system	IC411 self ventilated			
31	Bearing DE/NDE	6205-2Z/C3 - 6204-2Z/C3			
32	Type of Grease	Greased for life			
33	Sound pressure level (LP dB(A) 1m)	69	dB(A)		at load
34	Moment of inertia J = ¼ GD ²	0.00254	kg-m ²		
35	Balancing	Half Key			
36	Vibration class	Grade A			
37	Position of terminal box	Top			
38	Terminal box entries; no, dimens.	2xM32x1.5			
39	Number of power terminals	6			
40	Direction of rotation	CW or CCW			
41	Weight of rotor	3	kg		
42	Total weight of motor	24	kg		
43					

Variant Codes / Definition
332 = Baldor catalog number
333 = Not for use in the USA

Remarks:

Data based on situation 3/14/2012
All data subject to tolerances in accordance with IEC
Guaranteed values on request







ABB Motors and Generators		Technical Data Sheet - DOL				
		Project		Location		
Department/Author		Customer name		Customer ref.		Item name
Our ref.		Rev/Changed by	Date of issue	Saving ident		Pages 1(3)

No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	MM09152-PP (3GBP091322-ASB+332+333)			
3	Type/Frame	M3BP 90 SLB 2			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	1.5	kW		
6	Service factor	1			
7	Type of duty	S1(IEC) 100%			
8	Rated voltage U _N	400	VY	± 5 % (IEC 60034-1)	
9	Rated frequency f _N	50	Hz	± 2 % (IEC 60034-1)	
10	Rated speed n _N	2900	r/min		
11	Rated current I _N	3	A		
12	No-load current	1.05	A		
13	Starting current I _s /I _N	7.5		Fullfilled IEC 60034-12 design N,H	
14	Nominal torque T _N	4.9	Nm		
15	Locked rotor torque T _S /T _N	2.5			
16	Maximum torque T _{max} /T _N	2.6			
17	Minimum torque T _{min} /T _N	2			
18	Speed at minimum torque	690	r/min		
19	Load characteristics (IEC 60034-2-1:2007)	Load %	Current A	Efficiency %	Power factor
20	PLL determined from residual loss	100	3	82.2 / IE2	0.86
21		75	2.3	84.1	0.83
22		50	1.7	82.7	0.77
23		Start	22.9		0.62
24	Maximum starting time from hot	10	s		
25	Maximum starting time from cold	18	s		
26	Insulation class / Temperature class	F / B			
27	Ambient temperature	40	°C		
28	Altitude	1000	m.a.s.l.		
29	Enclosure	IP55			
30	Cooling system	IC411 self ventilated			
31	Bearing DE/NDE	6205-2Z/C3 - 6204-2Z/C3			
32	Type of Grease	Greased for life			
33	Sound pressure level (LP dB(A) 1m)	69	dB(A)	at load	
34	Moment of inertia J = ¼ GD2	0.00254	kg-m2		
35	Balancing	Half Key			
36	Vibration class	Grade A			
37	Position of terminal box	Top			
38	Terminal box entries; no, dimens.	2xM32x1.5			
39	Number of power terminals	6			
40	Direction of rotation	CW or CCW			
41	Weight of rotor	3	kg		
42	Total weight of motor	24	kg		
43					

Variant Codes / Definition
332 = Baldor catalog number
333 = Not for use in the USA

Remarks:

Data based on situation 3/14/2012
All data subject to tolerances in accordance with IEC
Guaranteed values on request






ABB Motors and Generators		Technical Data Sheet - DOL				
		Project		Location		
Department/Author		Customer name		Customer ref.		Item name
Our ref.		Rev/Changed by	Date of issue	Saving ident		Pages 1(3)

No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	MM09152-PP (3GBP091322-ASB+332+333)			
3	Type/Frame	M3BP 90 SLB 2			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	1.5	kW		
6	Service factor	1			
7	Type of duty	S1(IEC) 100%			
8	Rated voltage U _N	460	VY	± 5 % (IEC 60034-1)	
9	Rated frequency f _N	60	Hz	± 2 % (IEC 60034-1)	
10	Rated speed n _N	3505	r/min		
11	Rated current I _N	2.5	A		
12	No-load current	0.98	A		
13	Starting current I _s /I _N	8.6		Fullfilled IEC 60034-12 design N,H	
14	Nominal torque T _N	4.1	Nm		
15	Locked rotor torque T _S /T _N	2.5			
16	Maximum torque T _{max} /T _N	3			
17	Minimum torque T _{min} /T _N	2			
18	Speed at minimum torque	828	r/min		
19	Load characteristics (IEC 60034-2-1:2007)	Load %	Current A	Efficiency %	Power factor
20	PLL determined from residual loss	100	2.5	84.4 / IE2	0.87
21		75	2	84.2	0.83
22		50	1.53	81.6	0.75
23		Start	22		0.6
24	Maximum starting time from hot	10	s		
25	Maximum starting time from cold	18	s		
26	Insulation class / Temperature class	F / B			
27	Ambient temperature	40	°C		
28	Altitude	1000	m.a.s.l.		
29	Enclosure	IP55			
30	Cooling system	IC411 self ventilated			
31	Bearing DE/NDE	6205-2Z/C3 - 6204-2Z/C3			
32	Type of Grease	Greased for life			
33	Sound pressure level (LP dB(A) 1m)	76	dB(A)	at load	
34	Moment of inertia J = ¼ GD2	0.00254	kg-m2		
35	Balancing	Half Key			
36	Vibration class	Grade A			
37	Position of terminal box	Top			
38	Terminal box entries; no, dimens.	2xM32x1.5			
39	Number of power terminals	6			
40	Direction of rotation	CW or CCW			
41	Weight of rotor	3	kg		
42	Total weight of motor	24	kg		
43					

Variant Codes / Definition
332 = Baldor catalog number
333 = Not for use in the USA

Remarks:
Data based on situation 3/14/2012
All data subject to tolerances in accordance with IEC
Guaranteed values on request





ABB Motors and Generators	Starting Curves		ABB
	Project	Location	
Department/Author	Customer name	Customer ref.	Item name
Our ref.	Rev/Changed b	Date of issue	Saving ident
			Pages 3(3)

Type of product	TEFC, 3-phase, squirrel cage induction motor		
Type/Frame	M3BP 90 SLB 2		
Product code	MM09152-PP	Frequency (Hz)	60
Rated output P_N	1.5 kW	Rated current I_N	2.5 A
Type of duty	S1(IEC) 100%		

J_{motor} (kgm ²)	0.0025	Voltage (V) 100%	460	Voltage (V)	460V(100%)
J_{load} (kgm ²)		T_{start}/T_N	2.5	T_{start}/T_N	2.5
Speed (r/min)	3505	Starting time (s)		Run-up time (s)	
T_N (Nm)	4.1	Speed (r/min)		Speed (r/min)	
T_{load} (Nm)		I_s/I_N	8.6	I_s/I_N	8.6
Nbr. of consecutive starts		T_{max}/T_N	3	T_{max}/T_N	3



Load characteristics (IEC 60034-2-1:2007)
Data based on situation 3/14/2012
All data subject to tolerances in accordance with IEC