

ABB BALDOR RELIANCE III

Customer information packet

RM3007A

.33HP, 1725RPM, 3PH, 60HZ, 48, 3413M, OPEN, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	48
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.330 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Resilient
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	.800 A @ 460.0 V 1.600 A @ 230.0 V 1.800 A @ 208.0 V 2.000 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	68.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Resilient Mount

Part Detail

Revision	H
Type	AC
Mech. spec.	34K015
Base	
Status	PRD/A
Elec. spec.	34WGS872
Layout	34LYK015
Eff. date	10-28-2024
CD Diagram	CD0007
Poles	04
Leads	12#18
Proprietary	False
Created date	09-27-2013

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	0.8 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Terminal Panel Or Lead Hole
Motor Lead Quantity/Wire Size	12 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3413M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	10.34 IN
Power Factor	57
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Resilient Mount
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.500 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	SB
Winding Thermal 2	None

Nameplate

NP1257L											
CAT.NO.	RM3007A										
SPEC.	34K015S872G2										
HP	.33										
VOLTS	208-230/460										
AMP	1.8-1.6/.8										
RPM	1725										
FRAME	48				HZ		60		PH		3
SER.F.	1.25		CODE		L	DES		B	CL		B
NEMA-NOM-EFF	68		PF		57						
RATING	40C AMB-CONT										
CC											
DE	6203		ODE		6203						
ENCL	OPEN		SN								
	SFA 2-1.8/.9										

AC Induction Motor Performance Data

Record # 43524

Typical performance - not guaranteed values

Winding: 34WGS872-R004			Type: 3413M		Enclosure: OPEN	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		.33	Full Load Torque		1 LB-FT	
Volts		208-230/460	Start Configuration		direct on line	
Full Load Amps		1.8-1.6/.8	Breakdown Torque		4.7 LB-FT	
R.P.M.		1725	Pull-up Torque		3.35 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		3.75 LB-FT
NEMA Design Code		B	KVA Code		L	
Service Factor (S.F.)		1.25	Starting Current		4.4 A	
NEMA Nom. Eff.		68	Power Factor		57	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		
S.F. Amps		2-1.8/.9		Temp. Rise @ S.F. Load		

Load Characteristics 460 V, 60 Hz, 0.33 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	26	37	47	57	67	68	67
Efficiency	44.1	59	65.1	68	68.2	67	67.6
Speed	1788	1770	1760	1745	1730	1710	1722
Line amperes	0.7	0.73	0.77	0.8	0.85	1	0.91


ABB Motors and Mechanical Inc.


WINDING # 34WGS872

Typical performance - not guaranteed values.



0.33 HP 3 PH 60 HZ 1725 RPM 460 V 3413M

TORQUES (LB-FT) : PO=4.7 PU=3.35 LR=3.75 LRA=4.4





CD0007



- NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 2. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0007

REV. DESC: ADDED "CK" PLANT CODE			
REV. LTR: E	BY: EAH	REVISED: 05/06/99 17:1	TDR: 0181040
L00000		FILE: AAA00008370	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, THERMAL, 12 LEADS