

ABB BALDOR RELIANCE III

Customer information packet

SPM3215T

2HP, 1175RPM, 3PH, 60HZ, 184T, 3648M, OPSB, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	184T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM 4 WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.300 A @ 460.0 V 6.600 A @ 230.0 V 7.000 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	3.3 a

Part Detail

Revision	C
Type	AC
Mech. spec.	36P391
Base	
Status	PRD/A
Elec. spec.	36WGM001
Layout	36LYP391
Eff. date	06-07-2024
CD Diagram	CD0005
Poles	06
Leads	9#16
Proprietary	False
Created date	09-07-2023

Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	M
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3648M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	18.43 IN
Power Factor	64
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1175 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4423A01A01L															
CAT #	SPM3215T					WGT	101		LBS						
SPEC	36P391M001					ENCL	OPSB								
SER #						CC	010A		IP	22					
HP	2		MAG CUR			4.3/2.15									
VOLTS	230/460					NEMA NOM. EFF					89.5				
AMPS	6.6/3.3						PF	64							
RATING	40C AMB-CONT														
RPM	1175					MAX RPM		1800							
FRAME	184T		HZ	60		CODE	M		CLASS	F					
SER.F.	1.15		SF AMP	7.2/3.6				PH	3		DES	B			
DE	6206			ODE	6205										
LUBRICATION	POLYREX EM														
ID LOGO	INVERTER TYPE			VPWM		CHP	60		TO	90		1.5:1			
ID LOGO	WK2	0.451		CT	6		TO	60		10:1					
ID LOGO	SL HZ	1.25		VT	3		TO	60		20:1					
							QR								
YR															

AC Induction Motor Performance Data

Record # 100904

Preliminary Data Sheet

Winding: 36WGM001-R001			Type: 3648M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		2	Full Load Torque		8.92 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		6.6/3.3	Breakdown Torque		36.7 LB-FT		
R.P.M.		1175	Pull-up Torque		19.4 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		25.3 LB-FT	
NEMA Design Code		B	KVA Code		M		
Service Factor (S.F.)		1.15	No-load Current		2.14 A		
NEMA Nom. Eff.		89.5	Power Factor		64		
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		32°C
S.F. Amps		7.2/3.6			Temp. Rise @ S.F. Load		37°C
					Locked-rotor Power Factor		27.9
					Rotor inertia		0.451 lb-ft²

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	26	44	55	64	69	73	67
Efficiency	79.2	87	89	89.5	89.3	88.3	89.4
Speed	1196	1191	1184	1178	1170	1162	1173
Line amperes	2.23	2.49	2.84	3.28	3.79	4.38	3.59


ABB Motors and Mechanical Inc.


WINDING # 36WGM001

Typical performance - not guaranteed values.




2 HP 3 PH 60 HZ 1175 RPM 460 V 3648M

TORQUES (LB-FT): PO=36.7 PU=19.4 LR=25.3 LRA=24.9





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005