Customer information packet

SPM3313T

10HP, 1770RPM, 3PH, 60HZ, 215T, 3750M, OPSB, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 4:54:29 AM

Specifications

Enclosure	OPSB
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	WEEE
	NEMA PREMIUM 4
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	12.100 A @ 460.0 V
	24.200 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	12.1 a
Insulation Class	F

Part Detail

Revision	C
Type	AC
Mech. spec.	37T645
Base	
Status	PRD/A
Elec. spec.	37WGZ671
Layout	37LYT645
Eff. date	05-03-2024
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	09-05-2023

Inverter Code	Inverter Duty
KVA Code	J
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3750M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.20 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4423A01A01L												
CAT #	SPM3313T			**WGT**	158	**LBS**						
SPEC	37T645Z671			**ENCL**	OPSB							
SER #				**CC**	010A	**IP**	22					
HP	10			**MAG CUR**	10.2/5.1							
VOLTS	230/460					**NEMA NOM. EFF**	92.4					
AMPS	24.2/12.1					**PF**	82					
RATING	40C AMB-CONT											
RPM	1770					**MAX RPM**	2700					
FRAME	215T	**HZ**	60	**CODE**	J	**CLASS**	F					
SER.F.	1.15	**SF AMP**	27.6/13.8			**PH**	3	**DES**	A			
DE	6307			**ODE**	6206							
LUBRICATION	POLYREX EM											
ID LOGO	**INVERTER TYPE**			**VPWM**		**CHP**	60	**TO**	90	1.5:1		
ID LOGO	**WK2**	1.18	**CT**	6	**TO**	60		10:1				
ID LOGO	**SL HZ**	1	**VT**	3	**TO**	60		20:1				
						QR						
YR												

AC Induction Motor Performance Data
Record # 96652
Typical performance - not guaranteed values

Winding: 37WGZ671-R001	**Type:** 3750M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	29.83 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			24.2/12.1	**Breakdown Torque**	105 LB-FT
R.P.M.			1770	**Pull-up Torque**	47.5 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	66.1 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	107 A
Service Factor (S.F.)			1.15	**No-load Current**	6.05 A
NEMA Nom. Eff.	92.4	**Power Factor**	82	**Line-line Res. @ 25ºC**	0.89616 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	36°C
S.F. Amps			27.6/13.8	**Temp. Rise @ S.F. Load**	44°C
				Locked-rotor Power Factor	35.2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	40	62	74	79	82	84	81
Efficiency	87.9	92.1	92.9	92.7	92	91.2	92.3
Speed	1793.1	1787.3	1781.1	1774.3	1767.2	1759.6	1770
Line amperes	6.71	8.27	10.4	12.8	15.5	18.4	14.4


ABB Motors and Mechanical Inc.


WINDING # 37WGZ671

10 HP 3 PH 60 HZ 1770 RPM 460 V 3750M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=105 PU=47.5 LR=66.1 LRA=107




37LYT645
(717-735) = 16.32
(736-744) = 17.45
(745-750) = 18.20
(751-756) = 18.95
3.44
3.88
3.38
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
6 HOLES
Ø.43
5.50
.50
7.00
3.50
8.00
Ø9.57
7.90
LIFTING LUG
(1 EA. END)
10.04
5.25
5.19
LEAD
HOLE
Ø1.38
4.25
4.25
6.73
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: NEW
REV: - VERSION: 00 REVISED: 01:14:12 08/28/2023 TDR: 000001213521
MODEL NO. 37LYT645 REF: -
BY: USALMAZ B
BALDOR - RELIANCE®
HORZ 213-5T OPSB 37M, MOD NP
37LYT645

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS