

BALDOR • RELIANCE

Customer information packet

PCL3519M

3HP, 3450RPM, 1PH, 60HZ, 56C, 3532LC, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	3.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	12.500 A @ 230.0 V 13.700 A @ 208.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	78.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	12.5 a
Insulation Class	F

Part detail

Revision	AL
Type	AC
Mech. spec.	35T974
Base	
Status	PRD/A
Elec. spec.	35WGY870
Layout	35LYT974
Eff. date	05-07-2024
CD Diagram	CD0002A02
Poles	02
Leads	2#14 A PH,3#18 B&J
Proprietary	False
Created date	06-22-2007

Inverter Code	Not Inverter
KVA Code	G
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 14 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3532LC
Mounting Arrangement	F1
Number of Poles	2
Overall Length	14.12 IN
Power Factor	95
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Do Not Use
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Manual Thermal Overload
Winding Thermal 1 Location	KO
Winding Thermal 2	None

Nameplate

NP1257L									
CAT.NO.	PCL3519M								
SPEC.	35T974Y870								
HP	3								
VOLTS	230								
AMP	12.5								
RPM	3450								
FRAME	56C			HZ	60		PH	1	
SER.F.	1.15	CODE	G	DES	L	CL	F		
NEMA-NOM-EFF	85.5	PF	95						
RATING	40C AMB-CONT								
CC									
DE	6205	ODE	6203						
ENCL	TEFC	SN							

AC Induction Motor Performance Data

Record # 10351

Typical performance - not guaranteed values

Winding: 35WGY870-R001		Type: 3532LC		Enclosure: TEFC	
Nameplate Data			230 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)	3	Full Load Torque	4.6 LB-FT		
Volts	230	Start Configuration	direct on line		
Full Load Amps	12.5	Breakdown Torque	11.5 LB-FT		
R.P.M.	3450	Pull-up Torque	9.3 LB-FT		
Hz	60 Phase	1	Locked-rotor Torque	10.5 LB-FT	
NEMA Design Code	L KVA Code	G	Starting Current	77 A	
Service Factor (S.F.)	1.15	No-load Current	2.6 A		
NEMA Nom. Eff.	85.5 Power Factor	95	Line-line Res. @ 25°C	3.06 Ω A Ph 1.45 Ω B Ph	
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	47°C		
S.F. Amps		Temp. Rise @ S.F. Load	56°C		

Load Characteristics 230 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	76	87	92	92	93	92	93
Efficiency	72	80	85	85.5	82	78.5	85
Speed	3565	3540	3510	3475	3430	3370	3455
Line amperes	4.6	7.2	9.6	12.5	16	19.9	14.4


ABB Motors and Mechanical Inc.

WINDING # 35WGY870

Typical performance - not guaranteed values.

3 HP 1 PH 60 HZ 3450 RPM 230 V 3532LC

TORQUES (LB-FT): PO=11.5 PU=9.3 LR=10.5 LRA=77



3/26/2025 ACPERF, record # 10351

AC Induction Motor Performance Data

Record # 38571

Typical performance - not guaranteed values

Winding: 35WGY870-R001		Type: 3532LC		Enclosure: TEFC	
Nameplate Data			230 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)		3	Full Load Torque		4.65 LB-FT
Volts		230	Start Configuration		direct on line
Full Load Amps		12.5	Breakdown Torque		10.4 LB-FT
R.P.M.		3450	Pull-up Torque		8.29 LB-FT
Hz	60	Phase	1	Locked-rotor Torque	10.7 LB-FT
NEMA Design Code	L	KVA Code	G	Starting Current	79.3 A
Service Factor (S.F.)		1.15	No-load Current		1.97 A
NEMA Nom. Eff.	85.5	Power Factor	95	Line-line Res. @ 25°C	0.80257 Ω A Ph 1.4763 Ω B Ph
Rating - Duty		40C	AMB-CONT	Temp. Rise @ Rated Load	104°C
S.F. Amps				Temp. Rise @ S.F. Load	136°C

Load Characteristics 230 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	95	98	100	100	99	98	99
Efficiency	66.4	76.2	79.4	78.2	74.4	67.8	75.9
Speed	3553.8	3518.2	3479.4	3428.6	3362.2	3254.4	3389
Line amperes	4.09	6.62	9.37	12.7	16.6	22.2	15


ABB Motors and Mechanical Inc.

WINDING # 35WGY870

Typical performance - not guaranteed values.


3 HP 1 PH 60 HZ 3450 RPM 230 V 3532LC

TORQUES (LB-FT): PO=10.4 PU=8.29 LR=10.7 LRA=79.3



3/26/2025 ACPERF, record # 38571

CD0002A02



	LINE A	LINE B	JOIN
STD	1,8	4	J,5
OPP	1,5	4	J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REMOVE 2-TERMINAL THERMAL DETAIL, SEE CD0002A04		
REV. LTR: D	VERSION: 01	TDR: 000000360649
CD0002A02	FILE: \AAA\00007\520	REVISED: 17:11:40 04/15/2005
	MTL: -	BY: ENJOEPO

BALDOR ELECTRIC Co.

TYPE LC, SV, REV, THERMAL, 5 LEADS

CD0002A02