



---

# Customer information packet

## SPM3556T

1HP, 1170RPM, 3PH, 60HZ, 145T, 3532M, TEFC, F1

Class - None

Division - Not Applicable

## Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.320 A @ 230.0 V 3.500 A @ 208.0 V 1.660 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

## Part detail

Revision	C
Type	AC
Mech. spec.	35E6248
Base	
Status	PRD/A
Elec. spec.	35WGG824
Layout	35LYE6248
Eff. date	06-07-2024
CD Diagram	CD0005
Poles	06
Leads	9#18
Proprietary	False
Created date	09-08-2023

High Voltage Full Load Amps	1.7 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3532M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	14.19 IN
Power Factor	67
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1170 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

**Nameplate**

**NP4423A01A01L**

<b>CAT #</b>	SPM3556T	<b>WGT</b>	47	<b>LBS</b>			
<b>SPEC</b>	35E6248G824	<b>ENCL</b>	TEFC				
<b>SER #</b>		<b>CC</b>	010A	<b>IP</b>	54		
<b>HP</b>	1	<b>MAG CUR</b>	2.06/1.03				
<b>VOLTS</b>	230/460	<b>NEMA NOM. EFF</b>		84			
<b>AMPS</b>	3.32/1.66	<b>PF</b>	67				
<b>RATING</b>	40C AMB-CONT						
<b>RPM</b>	1170	<b>MAX RPM</b>	1800				
<b>FRAME</b>	145T	<b>HZ</b>	60	<b>CODE</b>	J	<b>CLASS</b>	F
<b>SER.F.</b>	1.15	<b>SF AMP</b>	3.68/1.84	<b>PH</b>	3	<b>DES</b>	B
<b>DE</b>	6205	<b>ODE</b>	6203				
<b>LUBRICATION</b>	POLYREX EM						
<b>ID LOGO</b>	<b>INVERTER TYPE</b>	<b>VPWM</b>	<b>CHP</b>	60	<b>TO</b>	90	1.5:1
<b>ID LOGO</b>	<b>WK2</b>	0.232	<b>CT</b>	6	<b>TO</b>	60	10:1
<b>ID LOGO</b>	<b>SL HZ</b>	1.57	<b>VT</b>	3	<b>TO</b>	60	20:1
<b>YR</b>							

**AC Induction Motor Performance Data**

Record # 100796

Typical performance - not guaranteed values

Winding: 35WGG824-R001		Type: 3532M	Enclosure: TEFC	
<b>Nameplate Data</b>			<b>460 V, 60 Hz: High Voltage Connection</b>	
Rated Output (HP)	1	Full Load Torque	4.47 LB-FT	
Volts	230/460	Start Configuration	direct on line	
Full Load Amps	2.06/1.03	Breakdown Torque	12.7 LB-FT	
R.P.M.	1170	Pull-up Torque	7.4 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque	9 LB-FT
NEMA Design Code	B KVA Code	J	Starting Current	9.5 A
Service Factor (S.F.)		1.15	No-load Current	1.03 A
NEMA Nom. Eff.	84 Power Factor	67	Line-line Res. @ 25°C	18.3 Ω
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	42°C
S.F. Amps	3.68/1.84		Temp. Rise @ S.F. Load	50°C
			Locked-rotor Power Factor	45.8
			Rotor inertia	0.232 lb-ft <sup>2</sup>

**Load Characteristics 460 V, 60 Hz, 1 HP**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	29	46	59	67	72	75	70
Efficiency	74.5	82.7	84.4	84.2	82.9	80.7	83.4
Speed	1193	1186	1179	1171	1162	1151	1166
Line amperes	1.08	1.21	1.41	1.66	1.96	2.32	1.84


ABB Motors and Mechanical Inc.

WINDING # 35WGG824


Typical performance - not guaranteed values.

1 HP 3 PH 60 HZ 1170 RPM 460 V 3532M

TORQUES (LB-FT): PO=12.7 PU=7.4 LR=9 LRA=9.5




7/23/2024 ACPERF, record # 100796



CD0005



LOW VOLTAGE (2Y)



LINE

HIGH VOLTAGE (1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS