

ABB BALDOR RELIANCE III

Customer information packet

RM3108A

.5 AIR OVERHP, 1725RPM, 3PH, 60HZ, 56, 3413M

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Resilient
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	.900 A @ 460.0 V 1.800 A @ 230.0 V 2.300 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	72.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Resilient Mount
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	M
Type	AC
Mech. spec.	34K019
Base	
Status	PRD/A
Elec. spec.	34WGR030
Layout	34LYK019
Eff. date	10-28-2024
CD Diagram	CD0007
Poles	04
Leads	12#18
Proprietary	False
Created date	04-05-2013

High Voltage Full Load Amps	0.9 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Terminal Panel
Motor Lead Quantity/Wire Size	12 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3413M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	10.97 IN
Power Factor	68
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Resilient Mount
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload



Winding Thermal 1 Location	SB
Winding Thermal 2	None

Nameplate

NP1257L										
CAT.NO.	RM3108A									
SPEC.	34K019R030G1									
HP	.5 AIR OVER									
VOLTS	230/460									
AMP	1.8/.9									
RPM	1725									
FRAME	56			HZ		60		PH	3	
SER.F.	1.25	CODE	J	DES	B	CL	B			
NEMA-NOM-EFF	72	PF	68							
RATING	40C AMB-CONT									
CC										
DE	6203	ODE	6203							
ENCL	OPEN	SN								
	SFA 2/1									

AC Induction Motor Performance Data

Record # 41850

Typical performance - not guaranteed values

Winding: 34WGR030-R001			Type: 3413M		Enclosure: OPAO		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		.5	Full Load Torque		1.51 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		1.8/.9	Breakdown Torque		4.56 LB-FT		
R.P.M.		1725	Pull-up Torque		2.77 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque		3.81 LB-FT		
NEMA Design Code		B	KVA Code		J	Starting Current	4.91 A
Service Factor (S.F.)		1.25	No-load Current		0.669 A		
NEMA Nom. Eff.		72	Power Factor		68	Line-line Res. @ 25°C	48.65 Ω
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load				
S.F. Amps		2/1	Temp. Rise @ S.F. Load				
			Locked-rotor Power Factor		69		
			Rotor inertia		0.031 LB-FT2		

Load Characteristics 460 V, 60 Hz, 0.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	31	46	58	68	74	79	74
Efficiency	55.9	74.4	77.4	77.4	77.8	75	77.8
Speed	1782	1767	1749	1729	1711	1685	1711
Line amperes	0.684	0.723	0.79	0.886	0.983	1.126	0.983


ABB Motors and Mechanical Inc.


WINDING # 34WGR030

Typical performance - not guaranteed values.



0.5 HP 3 PH 60 HZ 1725 RPM 460 V 3413M

TORQUES (LB-FT) : PO=4.56 PU=2.77 LR=3.81 LRA=4.91





CD0007



- NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 2. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: ADDED "CK" PLANT CODE			
REV. LTR: E	BY: EAH	REVISED: 05/06/99 17:1	TDR: 0181040
200000		FILE: AAA00008370	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, THERMAL, 12 LEADS

CD0007