


DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION
CAST IRON CONSTRUCTION

FRAMES 364TS-365TS

COOLING: FAN COOLED
ECP SEVERE DUTY

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: FOOT



MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STD. SHAFT EXTENSION IS .002 T.I.R. UP TO AND INCLUDING 1.625 DIA. AND .003 T.I.R. 1.625 DIA. TO 5 INCH DIA.

CONDUIT BOXES LOCATED ON OPPOSITE SIDE WHEN F-2, W-1, W-4, W-5, W-7, OR C-1 MOUNTING IS SPECIFIED

WEIGHT (LBS): 364T = 865
365T = 890

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CHANGED D/S TITLE TEXT FROM T TO TS EXTENSION			
REV: A	VERSION: 01	REVISED: 07:17:04 11/19/2024	TDR: 000001245078
MODEL NO. 617438-415			REF:
BY: USTIREE			B

BALDOR

HORZ 364-5TS TEFC ECP DIV.2, CL.2

617438-415

617438-415