ABB BALDOR RELIANCE

Customer information packet

SPM4310TS

60HP, 3555RPM, 3PH, 60HZ, 364TS, A36056M, TEFC
Class - CLI GP A,B,C,D; CLII GP F,G
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 6:14:35 AM

Specifications

Enclosure	TEFC
Frame	364TS
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D; CLII GP F,G
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	60.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
	CURUSEEV
	NEMA PREMIUM
	NEMA_PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	65.400 A @ 460.0 V
	145.000 A @ 208.0 V
	131.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.5 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	65.4 a
Insulation Class	F
Inverter Code	Inverter Duty

Part Detail

Revision	F
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG0224
Layout	617438-415
Eff. date	11-20-2025
CD Diagram	416820-002
Poles	02
Leads	3#4,6#6
Proprietary	False
Created date	09-20-2023

KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Max Speed	4200 rpm
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A36056M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	31.35 IN
Power Factor	91
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3555 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2496L
MOBILE POLYREX EM

NP4562L																				
CAT NO	SPM4310TS		**SPEC NO.**	A36-0003-0224			**I.P.**	55												
HP	60	**AMPS**	131/65.4		**VOLTS**	230/460		**DESIGN**	B											
FRAME SIZE	364TS	**RPM**	3555		**MAX RPM**	4200	**HZ**	60	**AMB**	40	**C**									
D.E. BRG.	65BC03J30X		**PH.3**	3	**DUTY**	CONT			**INSUL.CLASS**	F										
O.D.E. BRG.	65BC03J30X			**TYPE P**	P	**ENCL**	TEFC	**SF**	1.15	**CODE**	G									
POWER FACTOR	91		**MAX CORR KVAR**	5				**NEMA NOM EFFICIENCY**	94.5			**MOTOR WEIGHT**		**LBS**						
CL.I,DIV 2,GRP:	**A,B,C,D**	**T.CODE**	T3			**CL.1,ZONE 2,GRP:**			**IIA,IIB,IIC**	**T=**	200	**C**	**INVERTER T.CODE**	T3						
CL.II,DIV 2,GRP:	**F,G**	**T.CODE**	T3C			**CL II ZONE 22 GRPS IIIB**				**T=**	160	**C**	**INVERTER T.CODE**	T3						
ID LOGO	**INV TYPE:**	**VPWM**	**CT**	15	**TO**	60	**VT**	3	**TO**	60	**CHP**	60	**TO**	70						
ID LOGO	**1.0 SF VPWM**		**WK2**	6.7		**LBFT2**		**SL HZ**	0.75		**MAG CUR**	28.2/14.1								
SER.NO.						**MEETS INTENT OF IEEE-45**					**FOR WEATHER PROTECTION**									

S/O	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	364	60	P	3/60	3555	230/460

AMPS	DUTY	AMB °C/ INSUL	S.F.	NEMA DESIGN	CODE LETTER	ENCLOSURE
131/65.4	CONT	40/F	1.15	B	G	TEFC

E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES. @25 °C OHMS (BETWEEN LINES)
491281	418141005XE	---	---	.0254/.101

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	14.1	3600	7.60	0
1/4	15.0	20.9	3589	73.2	92.1
2/4	30.0	33.6	3579	88.4	94.7
3/4	45.0	48.8	3567	90.8	95.0
4/4	60.0	65.4	3555	90.7	94.6
5/4	75.0	82.7	3542	90.4	94.0

SPEED TORQUE


	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	205	182	431
PULL UP	1565	178	157	352
BREAKDOWN	3386	232	205	212
FULL LOAD	3555	100	88.6	65.4

AMPERES SHOWN FOR 460 VOLT CONNECTION. IF OTHER CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

TYPICAL DATA
XE MOTOR-NEMA NOM. EFF. 94.5 %
GUARANTEED MIN. EFF. 93.6%

ABB	DRAWN BY: W. L. SMITH CHECKED BY: G. R. WEBB APPROVED BY: E.J.CHRISTIAN DATE: 03/11/02	AC MOTOR PERFORMANCE DATA	A36WG0224-R004 DATE ISSUED 01/11/22


FRAME 364	RPM 3555	S.F. 1.15	ROTOR 418141005XE
HP 60	VOLTS 230/460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
TYPE P	AMPS 131/65.4	CODE LETTER G	TEST DATE ---
PHASE / HERTZ 3/60	DUTY CONT	ENCLOSURE TEFC	STATOR RES. @ 25°C .0254/.101
	AMB °C / INSUL 40/F	E/S 491281	OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 230/460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

ABB	DRAWN BY: W. L. SMITH CHECKED BY: G. R. WEBB APPROVED BY: E.J.CHRISTIAN DATE: 03/11/02	AC MOTOR PERFORMANCE DATA	A36WG0224-R004 ISSUE DATE 01/11/22

FRAME 364	RPM 3555	S.F. 1.15	ROTOR 418141005XE
HP 60	VOLTS 230/460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
TYPE P	AMPS 131/65.4	CODE LETTER G	TEST DATE ---
PHASE / HERTZ 3/60	DUTY CONT	ENCLOSURE TEFC	STATOR RES. @ 25°C .0254/.101
	AMB °C / INSUL 40/F	E/S 491281	OHMS (BETWEEN LINES)



THERMAL LIMIT CURVE
XE MOTOR-NEMA NOM. EFF. 94.5 %

AMPERES SHOWN FOR 230/460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

ABB	DRAWN BY: W. L. SMITH CHECKED BY: G. R. WEBB APPROVED BY: E.J.CHRISTIAN DATE: 03/11/02	AC MOTOR PERFORMANCE DATA	A36WG0224-R004 ISSUE DATE 01/11/22

DUTY MASTER ALTERNATING CURRENT MOTORS


SQUIRREL-CAGE INDUCTION
CAST IRON CONSTRUCTION

617438-415

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: FOOT

FRAMES 364TS-365TS

COOLING: FAN COOLED
ECP SEVERE DUTY



MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STD. SHAFT EXTENSION IS .002 T.I.R. UP TO AND INCLUDING 1.625 DIA. AND .003 T.I.R. 1.625 DIA. TO 5 INCH DIA.

CONDUIT BOXES LOCATED ON OPPOSITE SIDE WHEN F-2, W-1, W-4, W-5, W-7, OR C-1 MOUNTING IS SPECIFIED

WEIGHT (LBS): 364T = 865
365T = 890

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CHANGED D/S TITLE TEXT FROM T TO TS EXTENSION			
REV: A	VERSION: 01	REVISED: 07:17:04 11/19/2024	TDR: 000001245078
MODEL NO. 617438-415			REF:
BY: USTIREE			B


BALDOR


HORZ 364-5TS TEFC ECP DIV.2, CL.2

617438-415

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

416820-002

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1