

**BALDOR • RELIANCE**

---

# Customer information packet

## SPM30010

.5HP, 1725RPM, 3PH, 60HZ, 48, 3420M, ODP, F1, N

Class - None

Division - Not Applicable

## Specifications

Enclosure	ODP
Frame	48
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	WEEE C UR US
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	.750 A @ 460.0 V 1.500 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	81.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	0.8 a
Insulation Class	F

## Part detail

Revision	B
Type	AC
Mech. spec.	34B051
Base	
Status	PRD/A
Elec. spec.	34WGR771
Layout	34LYB051
Eff. date	03-18-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	09-12-2023

<b>Inverter Code</b>	Not Inverter
<b>KVA Code</b>	K
<b>Lifting Lugs</b>	No Lifting Lugs
<b>Locked Bearing Indicator</b>	No Locked Bearing
<b>Motor Lead Quantity/Wire Size</b>	9 @ 18 AWG
<b>Motor Lead Termination</b>	Flying Leads
<b>Motor Standards</b>	NEMA
<b>Motor Type</b>	3420M
<b>Mounting Arrangement</b>	F1
<b>Number of Poles</b>	4
<b>Overall Length</b>	10.25 IN
<b>Power Factor</b>	76
<b>Product Family</b>	General Purpose
<b>Pulley End Bearing Type</b>	Ball
<b>Pulley Face Code</b>	Standard
<b>Pulley Shaft Indicator</b>	Standard
<b>Rodent Screen</b>	None
<b>RoHS Status</b>	ROHS COMPLIANT
<b>Service Factor</b>	1.25
<b>Shaft Diameter</b>	0.500 IN
<b>Shaft Ground Indicator</b>	No Shaft Grounding
<b>Shaft Rotation</b>	Reversible
<b>Shaft Slinger Indicator</b>	No Slinger
<b>Speed</b>	1725 rpm
<b>Speed Code</b>	Single Speed
<b>Starting Method</b>	Direct on line
<b>Thermal Device - Bearing</b>	None
<b>Thermal Device - Winding</b>	None
<b>Vibration Sensor Indicator</b>	No Vibration Sensor
<b>Winding Thermal 1</b>	None
<b>Winding Thermal 2</b>	None

**Nameplate**

NP4558A02LL									
<b>CAT #</b>	SPM30010		<b>WGT</b>	27	<b>LBS</b>				
<b>SER #</b>			<b>ENCL</b>	ODP					
<b>SPEC</b>	34B051R771		<b>CC</b>		<b>IP</b>	22			
<b>HP</b>	.5		<b>NEMA NOM. EFF</b>			81.5			
<b>VOLTS</b>	230/460		<b>PF</b>	76					
<b>AMPS</b>	1.5/.75								
<b>RATING</b>	40C AMB-CONT								
<b>RPM</b>	1725		<b>PH</b>	3	<b>DES</b>	B			
<b>FRAME</b>	48	<b>HZ</b>	60	<b>CODE</b>	K	<b>CLASS</b>	F		
<b>SER.F.</b>	1.25	<b>SF AMP</b>	1.76/.88						
<b>DE</b>	6203		<b>ODE</b>	6203					
<b>GREASE</b>	POLYREX EM								
			<b>QR</b>						
<b>YR</b>									

**AC Induction Motor Performance Data**

Record # 100721

Preliminary Data Sheet

Winding: 34WGR771-R003		Type: 3420M	Enclosure: ODP
<b>Nameplate Data</b>		<b>460 V, 60 Hz: High Voltage Connection</b>	
Rated Output (HP)	.5	Full Load Torque	1.51 LB-FT
Volts	230/460	Start Configuration	direct on line
Full Load Amps	1.5/.75	Breakdown Torque	5.3 LB-FT
R.P.M.	1725	Pull-up Torque	3.5 LB-FT
Hz	60 Phase	Locked-rotor Torque	4.1 LB-FT
NEMA Design Code	B KVA Code	Starting Current	5.4 A
Service Factor (S.F.)	1.25	No-load Current	0.46 A
NEMA Nom. Eff.	81.5 Power Factor	Line-line Res. @ 25°C	30.4 Ω
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	22°C
S.F. Amps	1.76/.88	Temp. Rise @ S.F. Load	67°C
		Locked-rotor Power Factor	54.5
		Rotor inertia	0.0476 lb-ft <sup>2</sup>

**Load Characteristics 460 V, 60 Hz, 0.5 HP**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	37	56	69	76	80	82	80
Efficiency	66.3	77.5	81.1	81.9	81.7	80.6	81.7
Speed	1779	1762	1744	1725	1704	1681	1704
Line amperes	0.48	0.55	0.63	0.75	0.88	1.03	0.88


ABB Motors and Mechanical Inc.

WINDING # 34WGR771


0.5 HP 3 PH 60 HZ 1725 RPM 460 V 3420M

Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=5.3 PU=3.5 LR=4.1 LRA=5.4



7/23/2024 ACPERF, record # 100721



CD0005



LOW VOLTAGE  
(2Y)



LINE

HIGH VOLTAGE  
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

3PH, DV, 9 LEADS

CD0005