

# DUTY MASTER ALTERNATING CURRENT MOTORS

ENCLOSURE: TOTALLY ENCLOSED





MOUNTING: FOOT, F-1

SQUIRREL-CAGE INDUCTION

FRAME G447T  
INCLUDES G445T FRAME MOUNTING HOLES  
WITH TACONITE SLINGERS

COOLING: FAN COOLED

ENCLOSURE ENHANCEMENT: SEVERE DUTY



(1) OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF  
STANDARD SHAFT EXTENSION IS .003" T.I.R.

WEIGHT (LBS): 2515 - MAY VARY BY 15% DEPENDING ON RATING

DIMENSIONS ARE IN INCHES

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: NEW			
REV: -	VERSION: 00	REVISED: 11:49:01 10/11/2023	TDR: 000001213524
MODEL NO. 617439-175		REF:	
BY: ENSTEK0		Material:	

**BALDOR**

G447/445T TEFC F1 FT CAST IRON BOX DIV 2 CL 2