ABB BALDOR RELIANCE

Customer information packet

SPM44304TS-4

300HP, 1790RPM, 3PH, 60HZ, L449TS, A44192M, TE
Class - CLI GP A,B,C,D; CLII GP F,G
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/22/2026 4:08:53 PM

Specifications

Enclosure	TEFC
Frame	L449TS
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D; CLII GP F,G
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	300.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CURUSEEV CCSAUSEEV NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	342.000 A @ 460.0 V
Design Code	B
Duty Rating	CONT
Efficiency @ 100% Load	96.8 %
Feedback Device	NO FEEDBACK
Frame Prefix	L
Heater Indicator	No Heater
High Voltage Full Load Amps	342.0 a
Insulation Class	H
Inverter Code	Inverter Duty
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	12 @ 1 AWG

Part Detail

Revision	D
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG6743
Layout	617439-226
Eff. date	01-28-2025
CD Diagram	416820-036
Poles	04
Leads	3#1 (04 per group) Y
Proprietary	False
Created date	03-22-2024

Motor Standards	NEMA
Motor Type	A44192M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	56.71 IN
Power Factor	86
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	3.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1790 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2496L
MOBIL POLYREX EM

NP4562L												
CAT NO	SPM44304TS-4	**SPEC NO.**	A44-5012-6743	**I.P.**	55							
HP	300	**AMPS**	342	**VOLTS**	460	**DESIGN**	A					
FRAME SIZE	L449TS	**RPM**	1790	**MAX RPM**	2700	**HZ**	60	**AMB**	40			
D.E. BRG.	90BC03J30X	**PH.3**	3	**DUTY**	CONT	**INSUL.CLASS**	H					
O.D.E. BRG.	90BC03J30X	**TYPE P**	P	**ENCL**	TEFC	**SF**	1.15	**CODE**	H			
POWER FACTOR	86	**MAX CORR KVAR**	62	**NEMA NOM EFFICIENCY**	96.8	**MOTOR WEIGHT**		**LBS**				
CL.I,DIV 2,GRP:	**A,B,C,D**	**T.CODE**	T2C	**CL.1,ZONE 2,GRP:**	**IIA,IIB,IIC**	**T=**	230	**INVERTER T.CODE**	T2C			
CL.II,DIV 2,GRP:	**F,G**	**T.CODE**	T3C	**CL II ZONE 22 GRPS IIIB**		**T=**	160	**INVERTER T.CODE**	T3C			
ID LOGO	**INV TYPE:**	**VPWM**	**CT**	30	**TO**	60	**VT**	3	**TO**	60	**CHP**	60	**TO**	90
ID LOGO	**1.0 SF VPWM**	**WK2**	126	**LBFT2**	**SL HZ**	0.3	**MAG CUR**	133				
SER.NO.		**MEETS INTENT OF IEEE-45**				**FOR WEATHER PROTECTION**						

DUTY MASTER ALTERNATING CURRENT MOTORS

617439-226

ENCLOSURE: TOTALLY ENCLOSED


SQUIRREL-CAGE INDUCTION


COOLING: FAN COOLED


MOUNTING: FOOT, F-1 SIDE


GL449TS/G449TS FRAME MOUNTING HOLES WITH TACONITE SLINGERS

ENCLOSURE ENHANCEMENT: SEVERE DUTY









1 OBSTUCTIONS MUST NOT ENCROACH ON AIR INLET.

2 GROUND HOLES QTY 1 1/2-13 TAP; QTY 1 3/8-16 TAP

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

DIMENSIONS ARE IN INCHES.
WEIGHT (LBS.) 3045, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

SHEET NUMBER 1 OF 1

617439-226

REV. DESC: UPDATE SHAFT DIMENSIONS			
REV: A	VERSION: 01	REVISED: 10:18:43 01/24/2025	TDR: 000001245256
MODEL NO. 617439-226			
BY: USJOSUL			C


BALDOR

GL449TS TEFC F1 FT SIDE CI BOX 6318 BRGS DIV 2 CL 2 AIR DEF

617439-226

416820–036

A–C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575–BA)

416820–036

REV. DESC: LOADED TO BUS, C/R 335225			BALDOR
REV. LTR: –	VERSION: 00	TDR: 000000538207	
FILE: \MGA\00000\682		REVISED: 11:54:06 04/30/2010	CONN DIAG – STANDARD 3 LEAD
MTL: –		BY: RAGRA	SH 1 of 1