ABB BALDOR RELIANCE

Customer information packet

SPM3607T

1.5HP, 1175RPM, 3PH, 60HZ, 182T, 3640M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/10/2026 6:30:40 AM

Specifications

Enclosure	TEFC
Frame	182T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	WEEE
	NEMA PREMIUM 4
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.500 A @ 460.0 V
	5.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	88.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.5 a
Insulation Class	F

Part Detail

Revision	C
Type	AC
Mech. spec.	36P394
Base	
Status	PRD/A
Elec. spec.	36WGR643
Layout	36LYP394
Eff. date	06-07-2024
CD Diagram	CD0005
Poles	06
Leads	9#16
Proprietary	False
Created date	09-07-2023

Inverter Code	Inverter Duty
KVA Code	M
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3640M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	18.04 IN
Power Factor	63
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1175 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4423A01A01L												
CAT #	SPM3607T			**WGT**	90	**LBS**						
SPEC	36P394R643			**ENCL**	TEFC							
SER #				**CC**	010A	**IP**	54					
HP	1.5			**MAG CUR**	3.4/1.7							
VOLTS	230/460					**NEMA NOM. EFF**	88.5					
AMPS	5/2.5					**PF**	63					
RATING	40C AMB-CONT											
RPM	1175					**MAX RPM**	1800					
FRAME	182T	**HZ**	60	**CODE**	M	**CLASS**	F					
SER.F.	1.15	**SF AMP**	5.5/2.75			**PH**	3	**DES**	B			
DE	6206			**ODE**	6205							
LUBRICATION	POLYREX EM											
ID LOGO	**INVERTER TYPE**			**VPWM**		**CHP**	60	**TO**	90	1.5:1		
ID LOGO	**WK2**	0.376	**CT**	6	**TO**	60		10:1				
ID LOGO	**SL HZ**	1.25	**VT**	3	**TO**	60		20:1				
						QR						
YR												

AC Induction Motor Performance Data
Record # 100911
Typical performance - not guaranteed values

Winding: 36WGR643-R003	**Type:** 3640M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1.5	**Full Load Torque**	6.69 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			5/2.5	**Breakdown Torque**	28.1 LB-FT
R.P.M.			1175	**Pull-up Torque**	15 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	19.6 LB-FT
NEMA Design Code	B	**KVA Code**	M	**Starting Current**	19.2 A
Service Factor (S.F.)			1.15	**No-load Current**	1.69 A
NEMA Nom. Eff.	88.5	**Power Factor**	63	**Line-line Res. @ 25ºC**	5.99 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	40°C
S.F. Amps			5.5/2.75	**Temp. Rise @ S.F. Load**	46°C
				Locked-rotor Power Factor	29.1
				Rotor inertia	0.376 lb-ft²

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	26	43	55	63	68	72	66
Efficiency	76.1	85.2	87.7	88.5	88.4	88	88.4
Speed	1196	1191	1184	1178	1170	1163	1173
Line amperes	1.75	1.94	2.2	2.52	2.9	3.34	2.75


ABB Motors and Mechanical Inc.


WINDING # 36WGR643

1.5 HP 3 PH 60 HZ 1175 RPM 460 V 3640M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=28.1 PU=15 LR=19.6 LRA=19.2




36LYP394
614-623 = 15.18
624-634 = 16.55
635-646= 18.04
647-648 = 18.48
4.27
3.56
2.75
Ø8.60
.25 KEY
1.75 LONG
Ø 1.1250
1.1245
DRAIN FITTINGS
(EA. END)
6 HOLES
.41 DIA.
4.50
.50
5.50
2.75
6.50
Ø7.87
6.88
3.93
2.42
8.43
4.50 +.00 -.06
LEAD HOLE
1.09 DIA.
3.75
3.75
5.76
4.31
8.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD STACK 647-648
REV: A
VERSION: 01
REVISED: 01:48:59 11/14/2023
TDR: 000001216703
MODEL NO. 36LYP394
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
HORZ 182-4T TEFC 36M IP54, GFL BRGS, 'A64 NP, IBOLT
36LYP394

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS