ABB BALDOR RELIANCE

Customer information packet

SPM3711T

10HP, 3500RPM, 3PH, 60HZ, 215T, 3756M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 3:08:24 AM

Specifications

Enclosure	TEFC
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	WEEE
	NEMA PREMIUM 4
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	10.300 A @ 460.0 V
	20.600 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	10.3 a
Insulation Class	F


Part Detail

Revision	B
Type	AC
Mech. spec.	37T646
Base	
Status	PRD/A
Elec. spec.	37WGR482
Layout	37LYT646
Eff. date	07-02-2024
CD Diagram	CD0005
Poles	02
Leads	9#12
Proprietary	False
Created date	09-05-2023


Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	5400 rpm
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3756M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	20.52 IN
Power Factor	97
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None


Nameplate

NP4423A01A01L												
CAT #	SPM3711T			**WGT**	187	**LBS**						
SPEC	37T646R482			**ENCL**	TEFC							
SER #				**CC**	010A	**IP**	54					
HP	10		**MAG CUR**	5.8/2.9								
VOLTS	230/460					**NEMA NOM. EFF**	91.7					
AMPS	20.6/10.3				**PF**	97						
RATING	40C AMB-CONT											
RPM	3500			**MAX RPM**	5400							
FRAME	215T	**HZ**	60	**CODE**	K	**CLASS**	F					
SER.F.	1.15	**SF AMP**			**PH**	3	**DES**	A				
DE	6307		**ODE**	6206								
LUBRICATION	POLYREX EM											
ID LOGO	**INVERTER TYPE**		**VPWM**	**CHP**	60	**TO**	90	1.5:1				
ID LOGO	**WK2**	0.512	**CT**	6	**TO**	60	10:1					
ID LOGO	**SL HZ**	1.7	**VT**	3	**TO**	60	20:1					
						QR						
YR												


37LYT646
717-735 = 17.89
736-744 = 19.02
745-750 = 19.77
751-756 = 20.52
5.01
3.88
3.38
Ø 10.28
NAMEPLATE
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
6 HOLES
Ø.43
DRAIN FITTING
(EA. END)
5.50
.50
7.00
3.50
8.00
Ø 9.54
8.00
2.32
9.97
5.25
5.19
LEAD
HOLE
Ø1.38
4.25
4.25
6.76
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: NEW
REV: - VERSION: 00 REVISED: 02:44:47 08/28/2023 TDR: 000001213521
MODEL NO. 37LYT646 REF: -
BY: USALMAZ B
BALDOR - RELIANCE®
HORZ 213-5T TEFC 37M IP54, MOD NP
37LYT646

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS