

DUTY MASTER ALTERNATING CURRENT MOTORS  
SQUIRREL-CAGE INDUCTION

617435-555

ENCLOSURE: TOTALLY ENCLOSED





MOUNTING: FOOT, F-1 SIDE

G445T/G444T FRAME MOUNTING HOLES

COOLING: FAN COOLED

F  
E  
D  
C  
B  
A

F  
E  
D  
C  
B  
A



TACONITE SLINGER  
BOTH ENDS

DIMENSIONS ARE IN INCHES  
WEIGHT (LBS): 2130, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.  
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: ADDING FOOT MOUNTING DIMENSION			
REV: A	VERSION: 01	REVISED: 07:55:17 08/24/2018	TDR: 000001082568
MODEL NO. 617435-555		REF: -	
BY: USJEDIL		Material: -	

**BALDOR**

G445/444T TEFC FOOT F1/CAST IRON CONDUIT BOX/TACONITE

SHEET NUMBER  
1 OF 1

617435-555

1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.  
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

617435-555

C