



Customer information packet

SPM4410T-4

125HP, 1790RPM, 3PH, 60HZ, 444T, A4480M, TEFC

Class - CLI GP A,B,C,D; CLII GP F,G

Division - Division II

Specifications

Enclosure	TEFC
Frame	444T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D; CLII GP F,G
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	125.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV CURUSEEV NEMA PREMIUM NEMA_PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	142.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	96.2 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	142.0 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Max Speed	2700 rpm

Part detail

Revision	D
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG6731
Layout	617435-555
Eff. date	01-22-2025
CD Diagram	416820-036
Poles	04
Leads	3#2 Y
Proprietary	False
Created date	09-27-2023

Motor Lead Quantity/Wire Size	3 @ 2 AWG
Motor Standards	NEMA
Motor Type	A4480M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	44.96 IN
Power Factor	86
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	3.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1790 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate


NP2496L
MOBIL POLYREX EM

NP4562L

CAT NO	SPM4410T-4		SPEC NO.	A44-5011-6731		I.P.	55							
HP	125	AMPS	142	VOLTS	460	DESIGN	A							
FRAME SIZE	444T	RPM	1790	MAX RPM	2700	HZ	60	AMB	40					
D.E. BRG.	90BC03J30X		PH.3	3	DUTY	CONT		INSUL.CLASS	F					
O.D.E. BRG.	90BC03J30X		TYPE P	P	ENCL	TEFC	SF	1.15	CODE	H				
POWER FACTOR	86	MAX CORR KVAR	25.8		NEMA NOM EFFICIENCY	96.2		MOTOR WEIGHT		LBS				
CL.I,DIV 2,GRP:	A,B,C,D	T.CODE	T3C		CL.1,ZONE 2,GRP:	IIA, IIB, IIC		T=	160	INVERTER T.CODE	T3			
CL.II,DIV 2,GRP:	F,G	T.CODE	T3C		CL II ZONE 22 GRPS IIIB	T=		160	INVERTER T.CODE	T3C				
ID LOGO	INV TYPE:	VPWM	CT	30	TO	60	VT	3	TO	60	CHP	60	TO	90
ID LOGO	1.0 SF VPWM		WK2	52.8	LBFT2	SL HZ		0.41	MAG CUR	44.3				
SER.NO.					MEETS INTENT OF IEEE-45				FOR WEATHER PROTECTION					

416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682	REVISED: 11:54:06 04/30/2010	
MTL: -	BY: RAGRA	

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1