

ABB BALDOR RELIANCE III

Customer information packet

SUM71506-4

15HP, RPM, 3PH, 60HZ, 250TY, XPNV, V1

Class - CLI GP C,D

Division - Not Applicable

Specifications

Enclosure	XPNV
Frame	250TY
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Phase	3
Agency Approvals	CCSA US
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Cable Length	25 FOOT
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Haz Area Temp Code	T3C
Heater Indicator	No Heater
Insulation Class	F
Inverter Code	Not Inverter
IP Rating	IP68
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Motor Standards	NEMA
Motor Type	M
Mounting Arrangement	V1
Number of Poles	6
Product Family	Pump - Centrifugal
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	1.750 IN
Shaft Rotation	Reversible

Part Detail

Revision	F
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	78367
Layout	619738-005
Eff. date	12-10-2024
CD Diagram	416820-036
Poles	///
Leads	
Proprietary	False
Created date	05-20-2021

Shaft Slinger Indicator	No Slinger
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	Normally Closed Thermostat

Nameplate

000613007MS												
CAT.NO.	SUM71506-4			SPEC NO.		S25-CWS0-0005						
SER.NO.					FRAME SIZE		250TY					
CONSTANT HP RPM	HP	RPM	VOLTS		AMPS		HZ		S.F.			
	15	1170	230/460		42/21		6-60		1.00			
	15	1170	230/460		42/21		60		1.15			
	@		HZ		CODE	G						
	TYPE	P	INSUL.CLASS		F	TORQUE		10:1_VT			DESIGN	B
D.E. BRG.	60BC03JPP30A			ENCL	TENV		DUTY		15 MIN		PH	3
O.D.E. BRG.	40BC02JPG30A			MOTOR WEIGHT					AMB		40	
FINAL CONN VOLTAGE = 460 *15												
MIN IN AIR ;SUB. IN SEWAGE /												
WATER ONLY												

000613007RC			
CLASS I GROUP	C D X	NO.	
CLASS II GROUP	X X X		
OPERATING TEMP CODE	T3C		

000692000MB	
SUITABLE FOR OPERATION ON PWM	
INVERTER EQUIPPED WITH IGBT	
DEVICES AND CAPABLE OF	
CARRIER	
FREQUENCY OF 2 KHZ MINIMUM	

000613007MS

CAT.NO.	SUM71506-4	SPEC NO.	S25-CWS0-0005			
SER.NO.		FRAME SIZE	250TY			
	HP	RPM	VOLTS	AMPS	HZ	S.F.
	15	1170	230/460	42/21	6-60	1.00
	15	1170	230/460	42/21	60	1.15
CONSTANT HP RPM		@	HZ	CODE	G	
TYPE	P	INSUL.CLASS	F	TORQUE	10:1_VT	DESIGN B
D.E. BRG.	60BC03JPP30A	ENCL	TENV	DUTY	15 MIN	PH 3
O.D.E. BRG.	40BC02JPG30A	MOTOR WEIGHT		AMB	40	
FINAL CONN VOLTAGE = 460 *15						
MIN IN AIR ;SUB. IN SEWAGE /						
WATER ONLY						

AC induction motor performance data

Record #78367 - Typical performance - not guaranteed values

Winding	09WGA0123
Type	0946M
Enclosure	XPNV

Nameplate data

Rated Output	15		
Volts	230/460		
Full Load Amps	42/21		
R.P.M.	1170		
Hz	60	Phase	3
KVA Code	G		
S.F.	1.15		
NEMA Nom. Eff.	88.5	Power Factor	74
Duty	CONT		
S.F. Amps			

460 V, 60 Hz:

High Voltage Connection

Full Load Torque	67.1 LB-FT
Start Configuration	direct on line
Breakdown Torque	170 LB-FT
Pull-up Torque	78.2 LB-FT
Locked-rotor Torque	106 LB-FT
Starting Current	115 A
No-load Current	10.36
Line-line Res. @ 25°C	0.784 Ω
Temp. Rise @ Rated Load	49°C
Temp. Rise @ S.F. Load	62°C
Locked-rotor Power Factor	27.8
Rotor inertia	3.7 LB-FT ²

Load Characteristics 460 V, 60 Hz, 15 HP


% of Rated Load	NL	25	50	75	100	125	150	SF
Power Factor	5	36	56	66	71	72	71	72
Efficiency	0	85.4	89.8	90.1	89.6	87.9	85.5	88.6
Speed	1199	1193	1187	1180	1173	1162	1151	1166
Line amperes	10.36	11.45	13.94	17.7	21.99	27.45	34.1	25.3

SPEED TORQUE / SPEED CURRENT CURVES




09WGA0123

15HP 460V 60HZ



Record: 78367



416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)



416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682	REVISED: 11: 54: 06 04/30/2010	
MTL: -	BY: RAGRA	

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1

CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005