

ABB BALDOR RELIANCE III

Customer information packet

UCLE1015

10-15HP, 3500RPM, 1PH, 60HZ, 215Z, 3750LC, TEA

Class - None

Division - Not Applicable

Specifications

Enclosure	TEAO
Frame	215Z
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	15.000 HP @ 60 HZ 10.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	46.000 A @ 230.0 V
Drip Cover	No Drip Cover
Duty Rating	CONT
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	46.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K

Part Detail

Revision	T
Type	AC
Mech. spec.	37N421
Base	
Status	PRD/A
Elec. spec.	37WGY921
Layout	37LYN421
Eff. date	03-02-2026
CD Diagram	CD0208
Poles	02
Leads	2#8 A PH SEE NOTES, 2#14 B PH SEE NOTES
Proprietary	Y
Created date	False
	03-07-2014

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Pipe Or Pipe Adaptor
Motor Lead Quantity/Wire Size	2 @ 8 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3750LC
Mounting Arrangement	F1
Number of Poles	2
Overall Length	18.56 IN
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1279L									
CAT.NO.	UCLE1015								
SPEC.	37N421Y921G1								
HP	10-15								
VOLTS	230								
AMP	46-61								
RPM	3500								
FRAME	215Z		HZ	60		PH		1	
SER.F.	1.00		CODE	K	DES	-		CL	F
NEMA-NOM-EFF			PF						
RATING	40C AMB-CONT								
CC									
DE	6307		ODE	6206					
ENCL	TEAO		SN						

NP1263L									
CAT.NO.	UCLE1015								
SPEC.	37N421Y921G1								
HP	10-15								
VOLTS	230								
AMP	46-61								
RPM	3500								
FRAME	215Z			HZ	60		PH	1	
SER.F.	1.00	CODE	K	DES	-	CL	F		
NEMA-NOM-EFF		PF							
RATING	40C AMB-CONT								
CC									
DE	6307	ODE	6206						
ENCL	TEAO	SN							

Accessories

Part number	Description	Multiplier
37-3301FD	C FACE KIT FARM DUTY 213-5TC, ENCL, 6307	A8

AC Induction Motor Performance Data

Record # 12623

Typical performance - not guaranteed values

Winding: 37WGY921-R001			Type: 3750LC		Enclosure: TEAO		
Nameplate Data			230 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		10-15	Full Load Torque		22.5 LB-FT		
Volts		230	Start Configuration		direct on line		
Full Load Amps		46-61	Breakdown Torque		96 LB-FT		
R.P.M.		3500	Pull-up Torque		25.4 LB-FT		
Hz	60	Phase	1	Locked-rotor Torque		32.8 LB-FT	
NEMA Design Code		-	KVA Code	K	Starting Current		391 A
Service Factor (S.F.)			1	No-load Current		17.3 A	
NEMA Nom. Eff.		0	Power Factor	0	Line-line Res. @ 25°C		0.0724 Ω A Ph 0.851 Ω B Ph
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load			

Load Characteristics 230 V, 60 Hz, 15 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	70	85	89	91	91	90
Efficiency	76.8	85.9	88.1	87.8	86.7	84.3
Speed	3580	3562	3542	3518	3491	3456
Line amperes	23.3	34	46.9	61.2	77	94.6

ABB Motors and Mechanical Inc.

WINDING # 37WGY921

Typical performance - not guaranteed values.

15 HP 1 PH 60 HZ 3500 RPM 230 V 3750LC

TORQUES (LB-FT): PO=96 PU=25.4 LR=32.8 LRA=391





