

ABB BALDOR RELIANCE III

Customer information packet

SUM70506

5HP, 1145RPM, 3PH, 60HZ, 180TY, XPNV, V1

Class - CLI GP C,D

Division - Not Applicable

Specifications

Enclosure	XPNV
Frame	180TY
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Phase	3
Agency Approvals	CCSA US
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Haz Area Temp Code	T3C
Heater Indicator	No Heater
Insulation Class	F
Inverter Code	Not Inverter
IP Rating	IP68
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Motor Standards	NEMA
Motor Type	M
Mounting Arrangement	V1
Number of Poles	6
Product Family	Pump - Centrifugal
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	1.250 IN
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Part Detail

Revision	E
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	86085
Layout	619738-001
Eff. date	03-20-2025
CD Diagram	
Poles	///
Leads	
Proprietary	False
Created date	10-25-2021

Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	Normally Closed Thermostat

Nameplate

000613007MS										
CAT.NO.	SUM70506			SPEC NO.	S18-CWS0-0007					
SER.NO.					FRAME SIZE	180TY				
CONSTANT HP RPM	HP	RPM	VOLTS		AMPS		HZ		S.F.	
	5	1145	230/460		17.4/8.7		6-60		1.00	
	5	1145	230/460		17.4/8.7		60		1.15	
	@			HZ	CODE	J				
	TYPE	P	INSUL.CLASS		F	TORQUE	10:1_VT			DESIGN
	D.E. BRG.	50BC02JPP30A			ENCL	TENV	DUTY	15MIN		PH 3
O.D.E. BRG.	25BC02JPG30A			MOTOR WEIGHT			AMB		40	
	FINAL CONN VOLTAGE = 230 15									
	MIN IN AIR ;SUB. IN SEWAGE /									
	WATER ONLY									

000613007RC			
CLASS I GROUP	C D X	NO.	
CLASS II GROUP	X X X		
OPERATING TEMP CODE	T3C		

000692000MB	
SUITABLE FOR OPERATION ON PWM	
INVERTER EQUIPPED WITH IGBT	
DEVICES AND CAPABLE OF	
CARRIER	
FREQUENCY OF 2 KHZ MINIMUM	

000613007MS

CAT.NO.	SUM70506		SPEC NO.	S18-CWS0-0007		
SER.NO.			FRAME SIZE	180TY		
	HP	RPM	VOLTS	AMPS	HZ	S.F.
	5	1145	230/460	17.4/8.7	6-60	1.00
	5	1145	230/460	17.4/8.7	60	1.15
CONSTANT HP RPM		@	HZ	CODE	J	
TYPE	P	INSUL.CLASS	F	TORQUE	10:1_VT	DESIGN B
D.E. BRG.	50BC02JPP30A		ENCL	TENV	DUTY	15MIN PH 3
O.D.E. BRG.	25BC02JPG30A		MOTOR WEIGHT		AMB	40
	FINAL CONN VOLTAGE = 230 15					
	MIN IN AIR ;SUB. IN SEWAGE /					
	WATER ONLY					

AC induction motor performance data

Record #86085 - Typical performance - not guaranteed values

Winding	06WGA0016
Type	0640M
Enclosure	TENV

Nameplate data

Rated Output	5		
Volts	230/460		
Full Load Amps	17.4/8.7		
R.P.M.	1145		
Hz	60	Phase	3
KVA Code	J		
S.F.	1.15		
NEMA Nom. Eff.	88.5	Power Factor	68
Duty	15 MIN		
S.F. Amps			

460 V, 60 Hz:

High Voltage Connection

Full Load Torque	23.18 LB-FT
Start Configuration	direct on line
Breakdown Torque	65.61 LB-FT
Pull-up Torque	41.99 LB-FT
Locked-rotor Torque	51.39 LB-FT
Starting Current	45.18 A
No-load Current	5.45
Line-line Res. @ 25°C	3.05 Ω
Temp. Rise @ Rated Load	80°C
Temp. Rise @ S.F. Load	95°C
Locked-rotor Power Factor	36.8
Rotor inertia	0.372 lb-ft²

Load Characteristics 460 V, 60 Hz, 5 HP


% of Rated Load	NL	25	50	75	100	125	150	SF
Power Factor	5	27	44	56	64	68	71	66
Efficiency	0	77.7	86	87.7	88.5	85.5	82.9	86.7
Speed	1199	1189	1178	1166	1152	1136	1116	1748
Line amperes	5.45	5.74	6.38	7.4	8.68	10.38	12.37	9.7


SPEED TORQUE / SPEED CURRENT CURVES




06WGA0016

5HP 460V 60HZ





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005