

ABB BALDOR RELIANCE III

Customer information packet

VBM3538-D

.5/.37 KWHP, 1775RPM, 3PH, 60HZ, 56C, 3514M, T

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	C UR US CE CURUS UKCA WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.020 A @ 230.0 V 1.900 A @ 208.0 V 1.010 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	81.5 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	B
Type	AC
Mech. spec.	35X145
Base	
Status	PRD/A
Elec. spec.	35WGG069
Layout	35LYX145
Eff. date	01-12-2026
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	09-15-2023

Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3514M
Mounting Arrangement	F3
Number of Poles	4
Overall Length	16.25 IN
Power Factor	63
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None
--------------------------	-------------

Nameplate

NP1372L									
CAT.NO.	VBM3538-D								
SPEC.	35X145G069G4								
HP	.5/.37 KW								
VOLTS	208-230/460								
AMP	1.9-2.02/1.01								
R.P.M. (1/MIN)	1775								
FRAME	56C		HZ		60		PH		3
SER.F.	1.15	CODE		N	DES	B	CL	F	
NEMA-NOM-EFF	81.5	PF		63					
RATING	40C AMB-S1 CONT								
CC	IP44 IC411 20KG								
DE	6205		ODE		6205				
ENCL	TEFC	SN							
	IE2-79.0(75%)74.0(50%)								

AC Induction Motor Performance Data

Record # 101693

Typical performance - not guaranteed values

Winding: 35WGG069-R085			Type: 3514M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		.5	Full Load Torque		1.48 LB-FT		
Volts		208-230/460	Start Configuration		direct on line		
Full Load Amps		1.9-2.02/1.01	Breakdown Torque		8 LB-FT		
R.P.M.		1775	Pull-up Torque		4.4 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		5.1 LB-FT	
NEMA Design Code		B	KVA Code	N	Starting Current		8.4 A
Service Factor (S.F.)		1.15	No-load Current		0.85 A		
NEMA Nom. Eff.		81.5	Power Factor	63	Line-line Res. @ 25°C		30.3 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		23°C
S.F. Amps					Temp. Rise @ S.F. Load		25°C
					Locked-rotor Power Factor		66.8
					Rotor inertia		0.101 lb-ft²

Load Characteristics 460 V, 60 Hz, 0.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	24	37	48	58	65	71	62
Efficiency	58.9	72.5	78.4	80.5	81.6	81.5	81.2
Speed	1793	1788	1782	1776	1771	1763	1773
Line amperes	0.85	0.89	0.94	1.01	1.11	1.21	1.07


ABB Motors and Mechanical Inc.


WINDING # 35WGG069

0.5 HP 3 PH 60 HZ 1775 RPM 460 V 3514M

Typical performance - not guaranteed values.

TORQUES (LB-FT) : PO=8 PU=4.4 LR=5.1 LRA=8.4







CD2120

WIRING CONNECTIONS (1 PHASE VAC)

	POWER LINE A	POWER LINE B	CAP TOGETHER	CAP ALONE
AC LOW VOLT.	B1	B2	B3 & B5	B4
AC HIGH VOLT.	B1 & B5	B2	---	B3 CAP ALONE B4 CAP ALONE
DC VOLT.	B1	B2	B3 & B5	B4
				B1 WHITE B2 BLACK B3 GRAY B4 BLUE B5 RED

CD2120

REV. DESC: NEW		
REV. LTR: -	VERSION: 00	TDR: 000000741785
FILE: \CKA\00037\282	REVISED: 12: 28:11 04/12/2012	
MTL: -	BY: CKRONSO	

BALDOR • DODGE • RELIANCE
D-SERIES MOTOR BRAKE 5LD AC\DC
SH 1 of 1