

ABB BALDOR RELIANCE III

Customer information packet

VEBM3546-D

1/.75 KWHP, 1770 1/MIN IP44 IC411 22KGRPM

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CE CURUSEEV NEMA PREMIUM UKCA WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.200 A @ 230.0 V 3.200 A @ 208.0 V 1.600 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	G
Type	AC
Mech. spec.	35X145
Base	
Status	PRD/A
Elec. spec.	35WGG004
Layout	35LYX145
Eff. date	01-12-2026
CD Diagram	CD0005
Poles	04
Leads	9#18 Y
Proprietary	False
Created date	01-10-2022

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.6 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3520M
Mounting Arrangement	F3
Number of Poles	4
Overall Length	16.29 IN
Power Factor	69
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP2934L											
CAT.NO.	VEBM3546-D										
SPEC.	35X145G004G1										
HP	1/.75 KW										
VOLTS	230/460										
AMP	3.2/1.6										
R.P.M. (1/MIN)	1770										
FRAME	56C		HZ	60		PH	3				
SER.F.	1.15		CODE	N		DES	B		CL	F	
NEMA-NOM-EFF	85.5		PF	69							
RATING	40C AMB-S1 CONT										
CC	010A										
DE	6205		ODE	6205							
ENCL	TEFC		SN								
	IE2-85.4(75%)82.9(50%)										

AC Induction Motor Performance Data

Record # 91625

Typical performance - not guaranteed values

Winding: 35WGG004-R001			Type: 3520M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		1	Full Load Torque		2.982 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		3.2/1.6	Breakdown Torque		14.6 LB-FT		
R.P.M.		1770	Pull-up Torque		7.57 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		9.17 LB-FT	
NEMA Design Code		B	KVA Code	N	Starting Current		14.6 A
Service Factor (S.F.)		1.15	No-load Current		1.2 A		
NEMA Nom. Eff.		85.5	Power Factor	69	Line-line Res. @ 25°C		16.049 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		36°C
S.F. Amps		3.4/1.7	Temp. Rise @ S.F. Load		41°C		
			Locked-rotor Power Factor		61.549		
			Rotor inertia		0.144 lb-ft²		

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	29	45	58	67	73	78	71
Efficiency	71.1	81.2	84.7	85.8	86	85.6	85.9
Speed	1794	1787.3	1781.1	1774.3	1767.4	1759.4	1770
Line amperes	1.22	1.31	1.46	1.64	1.86	2.11	1.77


ABB Motors and Mechanical Inc.

WINDING # 35WGG004


Typical performance - not guaranteed values.


1 HP 3 PH 60 HZ 1770 RPM 460 V 3520M

TORQUES (LB-FT): PO=14.6 PU=7.57 LR=9.17 LRA=14.6



9/23/2026 ACPERF, record # 91625





CD2120

WIRING CONNECTIONS (1 PHASE VAC)

	POWER LINE A	POWER LINE B	CAP TOGETHER	CAP ALONE
AC LOW VOLT.	B1	B2	B3 & B5	B4
AC HIGH VOLT.	B1 & B5	B2	---	B3 CAP ALONE B4 CAP ALONE
DC VOLT.	B1	B2	B3 & B5	B4

B1 WHITE
 B2 BLACK
 B3 GRAY
 B4 BLUE
 B5 RED

CD2120

REV. DESC: NEW			BALDOR • DODGE • RELIANCE	
REV. LTR: -	VERSION: 00	TDR: 000000741785		
FILE: \CKA\00037\282		REVISED: 12:28:11 04/12/2012	D-SERIES MOTOR BRAKE 5LD AC\DC	
MTL: -		BY: CKRONSO	SH 1 of 1	