ABB BALDOR RELIANCE

Customer information packet

VEBM3546T-D

1/.75KWHP, 1770 1/MINRPM, 3PH, 60HZ, 143TC, 3
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
9/9/2026 2:33:54 PM

Specifications

Enclosure	TEFC
Frame	143TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CE
	CURUSEEV
	NEMA PREMIUM
	UKCA
	WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.200 A @ 230.0 V
	3.200 A @ 208.0 V
	1.600 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	H
Type	AC
Mech. spec.	35X050
Base	
Status	PRD/A
Elec. spec.	35WGG004
Layout	35LYX050
Eff. date	01-12-2026
CD Diagram	CD0005
Poles	04
Leads	9#18 Y
Proprietary	False
Created date	07-16-2021

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.6 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3520M
Mounting Arrangement	F3
Number of Poles	4
Overall Length	19.19 IN
Power Factor	69
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2934L								
CAT.NO.	VEBM3546T-D							
SPEC.	35X050G004G1							
HP	1/.75KW							
VOLTS	230/460							
AMP	3.2/1.6 IP44 IC411 24KG							
R.P.M. (1/MIN)	1770							
FRAME	143TC	**HZ**	60		**PH**	3		
SER.F.	1.15	**CODE**	N	**DES**	B	**CL**	F	
NEMA-NOM-EFF	85.5	**PF**	69					
RATING	40C AMB-CONT							
CC	010A							
DE	6205	**ODE**	6205					
ENCL	TEFC	**SN**						
	IE3-84.8(75%)81.6(50%)							

AC Induction Motor Performance Data
Record # 91625
Typical performance - not guaranteed values

Winding: 35WGG004-R001	**Type:** 3520M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1	**Full Load Torque**	2.982 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			3.2/1.6	**Breakdown Torque**	14.6 LB-FT
R.P.M.			1770	**Pull-up Torque**	7.57 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	9.17 LB-FT
NEMA Design Code	B	**KVA Code**	N	**Starting Current**	14.6 A
Service Factor (S.F.)			1.15	**No-load Current**	1.2 A
NEMA Nom. Eff.	85.5	**Power Factor**	69	**Line-line Res. @ 25ºC**	16.049 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	36°C
S.F. Amps			3.4/1.7	**Temp. Rise @ S.F. Load**	41°C
				Locked-rotor Power Factor	61.549
				Rotor inertia	0.144 lb-ft²

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	29	45	58	67	73	78	71
Efficiency	71.1	81.2	84.7	85.8	86	85.6	85.9
Speed	1794	1787.3	1781.1	1774.3	1767.4	1759.4	1770
Line amperes	1.22	1.31	1.46	1.64	1.86	2.11	1.77

ABB Motors and Mechanical Inc.

WINDING # 35WGG004

1 HP 3 PH 60 HZ 1770 RPM 460 V 3520M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=14.6 PU=7.57 LR=9.17 LRA=14.6





CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: ADD SECOND PLUG (WD4101A13) TO BOX			
REV: E	VERSION: 05	REVISED: 02:28:20 11/30/2020	TDR: 000001154873
MODEL NO: 35LYX050			REF: -
BY: USJOCUR	Material: -		B

BALDOR - RELIANCE®

VERT 143-5TC TEFC 35M W/DODGE 'D' SERIES #3-15 LB-FT BRAKE
SH 1 of 1

35LYX050

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS

CD2120

WIRING CONNECTIONS (1 PHASE VAC)

	POWER LINE A	POWER LINE B	CAP TOGETHER	CAP ALONE
AC LOW VOLT.	B1	B2	B3 & B5	B4
AC HIGH VOLT.	B1 & B5	B2	---	B3 CAP ALONE B4 CAP ALONE
DC VOLT.	B1	B2	B3 & B5	B4

B1 WHITE
B2 BLACK
B3 GRAY
B4 BLUE
B5 RED

CD2120

REV. DESC: NEW			BALDOR • DODGE • RELIANCE
REV. LTR: –	VERSION: 00	TDR: 000000741785	
FILE: \CKA\00037\282		REVISED: 12:28:11 04/12/2012	D–SERIES MOTOR BRAKE 5LD AC\DC
MTL: –		BY: CKRONS0	SH 1 of 1