

ABB BALDOR RELIANCE III

Customer information packet

VEBM3714T-D

10 /7.5KWHP, 1768RPM, 3PH, 60HZ, 215TC, 3750M

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CE CURUSEEV NEMA PREMIUM UKCA WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	27.000 A @ 208.0 V 24.800 A @ 230.0 V 12.400 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	A
Type	AC
Mech. spec.	37M909
Base	
Status	PRD/A
Elec. spec.	37WGZ711
Layout	37LYM909
Eff. date	07-18-2026
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	11-05-2025

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	12.4 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3750M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	26.86 IN
Power Factor	85
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1768 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP2934L											
CAT.NO.	VEBM3714T-D										
SPEC.	37M909Z711G1										
HP	10 /7.5KW										
VOLTS	230/460										
AMP	24.8/12.4										
R.P.M. (1/MIN)	1768										
FRAME	215TC		HZ	60		PH	3				
SER.F.	1.15		CODE	K		DES	A		CL	F	
NEMA-NOM-EFF	91.7		PF	85							
RATING	40C AMB-CONT										
CC	010A		IP44 IC411 80KG								
DE	6307		ODE	6206							
ENCL	TEFC		SN								
	IE3-92.7(75%)92.3(50%)										

AC Induction Motor Performance Data

Record # 115760

Typical performance - not guaranteed values

Winding: 37WGZ711-R001			Type: 3750M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		10	Full Load Torque		29.79 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		24.8/12.4	Breakdown Torque		93.4 LB-FT		
R.P.M.		1768	Pull-up Torque		44.7 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		55.5 LB-FT	
NEMA Design Code		A	KVA Code	K	Starting Current		90.5 A
Service Factor (S.F.)		1.15	No-load Current		5.11 A		
NEMA Nom. Eff.		91.7	Power Factor	85	Line-line Res. @ 25°C		1.1801 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		77°C
S.F. Amps		28.2/14.1	Temp. Rise @ S.F. Load		108°C		
			Locked-rotor Power Factor		37.2		

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	68	78	82	85	85	84
Efficiency	89.9	92.6	92.6	91.8	90.5	88.9	91
Speed	1792.4	1785	1776.3	1767.2	1756.7	1745.2	1756
Line amperes	5.83	7.54	9.79	12.4	15.3	18.6	14.2


ABB Motors and Mechanical Inc.


WINDING # 37WGZ711

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 1768 RPM 460 V 3750M

TORQUES (LB-FT): PO=93.4 PU=44.7 LR=55.5 LRA=90.5







CD2120

WIRING CONNECTIONS (1 PHASE VAC)

	POWER LINE A	POWER LINE B	CAP TOGETHER	CAP ALONE
AC LOW VOLT.	B1	B2	B3 & B5	B4
AC HIGH VOLT.	B1 & B5	B2	---	B3 CAP ALONE B4 CAP ALONE
DC VOLT.	B1	B2	B3 & B5	B4

B1 WHITE
 B2 BLACK
 B3 GRAY
 B4 BLUE
 B5 RED

CD2120

REV. DESC: NEW		
REV. LTR: -	VERSION: 00	TDR: 000000741785
FILE: \CKA\00037\282		REVISED: 12: 28:11 04/12/2012
MTL: -	BY: CKRONSO	

BALDOR • DODGE • RELIANCE
D-SERIES MOTOR BRAKE 5LD AC\DC
SH 1 of 1