

ABB BALDOR RELIANCE III

Customer information packet

VEBM3558T-S

2 /1.5KWHP, 1750RPM, 3PH, 60HZ, 145TC, 3526M

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	145TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CE CURUSEEV NEMA PREMIUM UKCA WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.800 A @ 208.0 V 5.200 A @ 230.0 V 2.600 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	-
Type	AC
Mech. spec.	35X067
Base	
Status	PRD/A
Elec. spec.	35WGZ165
Layout	35LYX067
Eff. date	02-19-2026
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	11-04-2025

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.6 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3526M
Mounting Arrangement	F3
Number of Poles	4
Overall Length	15.40 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2934L									
CAT.NO.	VEBM3558T-S								
SPEC.	35X067Z165G1								
HP	2 /1.5KW								
VOLTS	230/460								
AMP	5.6/2.8								
R.P.M. (1/MIN)	1760								
FRAME	145TC		HZ	60		PH	3		
SER.F.	1.15	CODE	K	DES	B	CL	F		
NEMA-NOM-EFF	86.5	PF	78						
RATING	40C AMB-CONT								
CC	010A		BRK	10FT-LB					
DE	6205	ODE	6205						
ENCL	TEFC	SN							
	IE3-87.6(75%) 86.5(50%)								

AC Induction Motor Performance Data

Record # 114535

Typical performance - not guaranteed values

Winding: 35WGZ165-R001			Type: 3526M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		2	Full Load Torque		5.979 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		5.2/2.6	Breakdown Torque		18.4 LB-FT		
R.P.M.		1750	Pull-up Torque		13.7 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		14.5 LB-FT	
NEMA Design Code		B	KVA Code		K		
Service Factor (S.F.)		1.15	No-load Current		1.24 A		
NEMA Nom. Eff.		86.5	Power Factor		82		
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		59°C
S.F. Amps		6/3			Temp. Rise @ S.F. Load		75°C
					Locked-rotor Power Factor		59.3

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	42	64	76	82	86	87	84
Efficiency	82.7	87.6	87.8	86.6	84.6	82	85.4
Speed	1788.4	1776.9	1763.5	1748.9	1731.7	1711.8	1739
Line amperes	1.35	1.65	2.09	2.61	3.21	3.91	2.97

ABB Motors and Mechanical Inc.

WINDING # 35WGZ165

Typical performance - not guaranteed values.

2 HP 3 PH 60 HZ 1750 RPM 460 V 3526M

TORQUES (LB-FT): PO=18.4 PU=13.7 LR=14.5 LRA=17.9





