ABB BALDOR RELIANCE

Customer information packet

VECP3774T

10HP, 1760RPM, 3PH, 60HZ, 215TC, 0748M, TEFC, F
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 10:43:05 PM

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CCSA US
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.3
Current @ Voltage	12.500 A @ 460.0 V
	25.000 A @ 230.0 V
Design Code	A
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	AD
Type	AC
Mech. spec.	07K370
Base	
Status	PRD/A
Elec. spec.	07WGX776
Layout	07LYK370
Eff. date	05-26-2026
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	07-25-2006

Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	12.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0748M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	21.36 IN
Power Factor	82
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line

Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3257								
CAT.NO.	VECP3774T							
SPEC.	07K370X776G1							
HP	10 TE							
VOLTS	230/460 ENCL TEFC							
AMP	25/12.5							
RPM	1760							
FRAME	215TC	**HZ**	60			**PH**	3	
SER.F.	1.15	**CODE**	H	**DES**	A	**CL**	F	
RATING	40C AMB-CONT							
SN								
DE	6307	**ODE**	6307					
NEMA-NOM-EFF	92.4	**PF**	82					
G.MIN.EFF	91.0	**CC**	010A					
T. CODE	T3C	**T=**	160					

NP3260					
SPEC.	07K370X776G1				
D.E. BRG.	35BC03XP30X				
O.D.E. BRG.	35BC03XP30X				
GREASE	POLYREX EM				
RPM MAX	2700	**MAX. KVAR**	1.7		
BLANK					
INV.TYPE	PWM				
T=	160				
C HP FR	60	**C HP TO**	90		
CT HZ FROM	1.3	**CT HZ TO**	60		
VT HZ FROM	0-	**VT HZ TO**	60		
HTR-VOLTS		**HTR-AMPS**			
HTR-WATTS		**MAX. SPACE HEATER TEMP.**			

AC Induction Motor Performance Data
Record # 25097
Typical performance - not guaranteed values

Winding: 07WGX776-R016	**Type:** 0748M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	29.8 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			25/12.5	**Breakdown Torque**	87 LB-FT
R.P.M.			1760	**Pull-up Torque**	51.9 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	57.5 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	88.5 A
Service Factor (S.F.)			1.15	**No-load Current**	5.12 A
NEMA Nom. Eff.	92.4	**Power Factor**	82	**Line-line Res. @ 25ºC**	0.973 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	60°C
S.F. Amps				**Temp. Rise @ S.F. Load**	76°C
				Locked-rotor Power Factor	35
				Rotor inertia	1.18 LB-FT2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	44	67	78	82	84	85	83
Efficiency	90	92.9	93.1	92.5	91.4	90.1	91.8
Speed	1790	1781	1771	1762	1750	1739	1755
Line amperes	5.84	7.52	9.75	12.3	15.2	18.3	14


ABB Motors and Mechanical Inc.


WINDING # 07WGX776

10 HP 3 PH 60 HZ 1760 RPM 460 V 0748M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=87 PU=51.9 LR=57.5 LRA=88.5




07LYK370
(717-750) = 21.35
10.23
3.12
PLUG
AUX NP
(WHEN REQ'D)
GREASE FITTING
W/CAP
(EA. END)
.26
.31 KEY
2.38 LONG
Ø12.19
8.500
8.497
9.06
Ø 1.3750
1.3745
FORSHEDA
SLINGER
SLINGER
GROUND
LUG
GREASE RELIEF
(EA. END)
DRAIN FITTING
(EA. END)
11.50
8.97
6.00
2.04
45°
45°
7.78
LEAD HOLE
1.00 N.P.T.
7.25
4 HOLES
.50-13 TAP
7.25Ø B.C.
OMIT LOCKWASHER
& COAT SCREWHEAD
WITH RED SEALER
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT FROM AUTOCAD TO SWD
REV: F
VERSION: 06
REVISED: 10:29:47 10/20/2023
TDR: 000001218940
MODEL NO. 07LYK370
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
STD VERT 213-5TC TEFC M CP W/6307 BRGS, LIPPED LID, DRIP CVR
07LYK370

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS