



---

# Customer information packet

## VECP3581T

1HP, 1770RPM, 3PH, 60HZ, 143TC, 0522M, TEFC, F1

Class - CLI GP A,B,C,D

Division - Division II

## Specifications

Enclosure	TEFC
Frame	143TC
Frame Material	Iron
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
XP Class and Group	CLI GP A,B,C,D
XP Division	Division II
Agency Approvals	CCSA US CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.2
Current @ Voltage	3.400 A @ 230.0 V 3.300 A @ 208.0 V 3.200 A @ 208.0 V 1.700 A @ 460.0 V
Design Code	B
Drip Cover	Drip Cover
Duty Rating	CONT

## Part detail

Revision	-
Type	AC
Mech. spec.	05F006
Base	
Status	PRD/A
Elec. spec.	05WGX903
Layout	05LYF006
Eff. date	12-13-2022
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	07-21-2022

Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.7 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	N
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0522M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.56 IN
Power Factor	69
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

<b>Thermal Device - Winding</b>	None
<b>Vibration Sensor Indicator</b>	No Vibration Sensor
<b>Winding Thermal 1</b>	None
<b>Winding Thermal 2</b>	None
<b>XP Temp Code</b>	T4

**Nameplate**

<b>NP3258</b>									
<b>CAT.NO.</b>	VECP3581T								
<b>SPEC.</b>	05F006X903G1								
<b>HP</b>	1 TE								
<b>VOLTS</b>	208-230/460								
<b>AMP</b>	3.3-3.4/1.7								
<b>RPM</b>	1770								
<b>FRAME</b>	143TC	<b>HZ</b>	60	<b>PH</b>	3				
<b>SER.F.</b>	1.15	<b>CODE</b>	N	<b>DES</b>	B	<b>CL</b>	F		
<b>RATING</b>	40C AMB-CONT								
<b>SN</b>									
<b>DE</b>	6205	<b>ODE</b>	6205						
<b>NEMA-NOM-EFF</b>	85.5	<b>PF</b>	69						
<b>G.MIN.EFF</b>	82.5	<b>CC</b>	010A						
<b>T. CODE</b>	T4	<b>T=</b>	135						

<b>NP3261</b>			
<b>SPEC.</b>	05F006X903G1		
<b>D.E. BRG.</b>	25BC02XP30X		
<b>O.D.E. BRG.</b>	25BC02XP30X		
<b>GREASE</b>	POLYREX EM		
<b>RPM MAX</b>	2700	<b>MAX. KVAR</b>	0.49
<b>BLANK</b>	SFA 3.6/1.8		
<b>INV.TYPE</b>	PWM		
<b>T=</b>	135		
<b>C HP FR</b>	60	<b>C HP TO</b>	90
<b>CT HZ FROM</b>	1.2	<b>CT HZ TO</b>	60
<b>VT HZ FROM</b>	-0	<b>VT HZ TO</b>	60
<b>HTR-VOLTS</b>		<b>HTR-AMPS</b>	
<b>HTR-WATTS</b>		<b>MAX. SPACE HEATER TEMP.</b>	SFA 1.86

**AC Induction Motor Performance Data**

Record # 87075

Preliminary Data Sheet

Winding: 05WGX903-R001		Type: 0522M		Enclosure: TEFC	
<b>Nameplate Data</b>			<b>460 V, 60 Hz: High Voltage Connection</b>		
Rated Output (HP)		1	Full Load Torque		2.97 LB-FT
Volts		208-230/460	Start Configuration		direct on line
Full Load Amps		3.3-3.4/1.7	Breakdown Torque		15.85 LB-FT
R.P.M.		1770	Pull-up Torque		9.1 LB-FT
Hz	60 Phase	3	Locked-rotor Torque		10.45 LB-FT
NEMA Design Code	B KVA Code	N	Starting Current		15.67 A
Service Factor (S.F.)		1.15	No-load Current		1.21 A
NEMA Nom. Eff.	85.5 Power Factor	69	Line-line Res. @ 25°C		14.1 Ω
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		24°C
S.F. Amps		3.6/1.8	Temp. Rise @ S.F. Load		27°C
			Locked-rotor Power Factor		60.1
			Rotor inertia		0.159 lb-ft <sup>2</sup>

**Load Characteristics 460 V, 60 Hz, 1 HP**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	27	43	56	65	72	76	69
Efficiency	70.7	81	84.4	85.8	85.9	85.5	85.9
Speed	1792	1785	1778	1771	1763	1755	1766
Line amperes	1.23	1.34	1.49	1.68	1.89	2.15	1.81


ABB Motors and Mechanical Inc.

WINDING # 05WGX903

Typical performance - not guaranteed values.


1 HP 3 PH 60 HZ 1770 RPM 460 V 0522M

TORQUES (LB-FT): PO=15.85 PU=9.1 LR=10.45 LRA=15.67



3/28/2023 ACPERF, record # 87075





REV. DESC: 05SF1101A54 WAS A04			
REV: E	VERSION: 05	REVISED: 12/23/41 02/01/2019	TDR: 000001096286
MODEL NO. 05LYF006		REF:	
BY: ENBILTO		B	

**BALDOR ELECTRIC Co.**

VER 143-5TC TEFC M CP W/6205 BRG EA.END, LIPPED LID, DRP CVR

05LYF006

CD0005




LOW VOLTAGE  
(2Y)



LINE

HIGH VOLTAGE  
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

3PH, DV, 9 LEADS