

ABB BALDOR RELIANCE III

Customer information packet

VECP83771T-4

10HP, 3475RPM, 3PH, 60HZ, 215TC, 0742M, TEFC, F

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CL I GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSA US CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	11.300 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	AD
Type	AC
Mech. spec.	07M323
Base	
Status	PRD/A
Elec. spec.	07WGY930
Layout	07LYM323
Eff. date	10-01-2025
CD Diagram	CD0006
Poles	02
Leads	3#14
Proprietary	False
Created date	08-21-2012

Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	11.3 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0742M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	20.24 IN
Power Factor	91
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4328									
CAT.NO.	VECP83771T-4								
SPEC.	07M323Y930G1								
HP	10 TE			IP	56				
VOLTS	460								
AMPS	11.3								
R.P.M.	3500								
FRAME	215TC		HZ	60		PH	3		
SER.F.	1.15	CODE	H	DES.	B	CLASS	F		
RATING	40C AMB-CONT								
SN									
DE	6307		ODE	6307					
NEMA NOM. EFF.	91		P.F.	91					
GUAR. MIN. EFF.	89.5		CC	010A					
T. CODE	T3C		TEMP=	160					

NP3186						
SPEC.	07M323Y930G1					
ABMA DE BRG	35BC03X30X					
ABMA ODE BRG	35BC03X30X					
GREASE	POLYREX EM					
MOTOR WEIGHT	225	ROTOR BARS	28	STATOR BARS	36	
MAX. R.P.M.	5400	MAX. KVAR	N/A			
INV.TYPE	PWM					
T=	160					
CHP	60	TO	90			
CT	6	TO	60			
VT	3	TO	60			
HTR-VOLTS	N/A	HTR-AMPS	N/A			
HTR-WATTS		MAX. SPACE HEATER TEMP.				N/A

AC Induction Motor Performance Data

Record # 47355

Typical performance - not guaranteed values

Winding: 07WGY930-R013				Type: 0742M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		10		Full Load Torque		14.8 LB-FT		
Volts		460		Start Configuration		direct on line		
Full Load Amps		11.3		Breakdown Torque		67.3 LB-FT		
R.P.M.		3500		Pull-up Torque		22.4 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		29 LB-FT		
NEMA Design Code		B		KVA Code	H		Starting Current	81 A
Service Factor (S.F.)		1.15		No-load Current		3.11 A		
NEMA Nom. Eff.		91		Power Factor	91		Line-line Res. @ 25°C	0.791 Ω
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load		50°C
S.F. Amps						Temp. Rise @ S.F. Load		62°C
						Locked-rotor Power Factor		30.3
						Rotor inertia		0.383 LB-FT ²

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	64	81	88	89	91	90	91
Efficiency	89.1	92.2	92.3	91.6	90.3	89.1	90.9
Speed	3576	3554	3530	3504	3474	3442	3486
Line amperes	4.08	6.21	8.61	11.3	14.1	17.4	13


ABB Motors and Mechanical Inc.

WINDING # 07WGY930

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 3500 RPM 460 V 0742M

TORQUES (LB-FT) : PO=67.3 PU=22.4 LR=29 LRA=81



AC Induction Motor Performance Data

Record # 65135

Typical performance - not guaranteed values

Winding: 07WGY930-R013			Type: 0742M		Enclosure: TEFC		
Nameplate Data			368 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		10	Full Load Torque		15.02 LB-FT		
Volts		460	Start Configuration		direct on line		
Full Load Amps		11.3	Breakdown Torque		42.64 LB-FT		
R.P.M.		3500	Pull-up Torque		14.18 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		18.36 LB-FT	
NEMA Design Code		B	KVA Code	H	Starting Current		64.41 A
Service Factor (S.F.)		1.15		No-load Current		2.43 A	
NEMA Nom. Eff.		91	Power Factor	91	Line-line Res. @ 25°C		0.791 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		66°C	
S.F. Amps				Temp. Rise @ S.F. Load		87°C	
				Locked-rotor Power Factor		30.1	
				Rotor inertia		0.383 LB-FT2	

Load Characteristics 368 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	79	89	91	90	90	86	90
Efficiency	90.5	92.3	91.4	89.7	87.4	84.6	88.3
Speed	3565	3532	3495	3453	3401	3335	3422
Line amperes	4.09	7.1	10.43	14.25	18.44	23.94	16.8


ABB Motors and Mechanical Inc.


WINDING # 07WGY930

Typical performance - not guaranteed values.




10 HP 3 PH 60 HZ 3500 RPM 368 V 0742M

TORQUES (LB-FT): PO=42.64 PU=14.18 LR=18.36 LRA=64.41





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1