ABB BALDOR RELIANCE

Customer information packet

VEDM3558

2HP, 1760RPM, 3PH, 60HZ, 56C, 3528M, TEFC, F1, N
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 3:16:36 PM

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CCSA US
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	5.800 A @ 208.0 V
	5.600 A @ 230.0 V
	2.800 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	C
Type	AC
Mech. spec.	35E4312
Base	
Status	PRD/A
Elec. spec.	35WGG073
Layout	35LYE4312
Eff. date	05-30-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-10-2022

Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.8 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3528M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.23 IN
Power Factor	77
Product Family	Dirty Duty Plus
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3504								
CAT NO	VEDM3558							
SPEC.	35E4312G073G1			**ENCL**	TEFC			
FRAME	56C	**HP**	2					
VOLTS	230/460							
FLA	5.6/2.8			**I.P.**	56			
RPM	1760	**RPM MAX**	2700					
HZ	60	**PH**	3	**CLASS**	F			
SER.F.	1.15	**DES**	B	**CC**	010A			
NEMA-NOM-EFF	86.5							
RATING	40C AMB-CONT							
DE BRG	6205	**ODE BRG**	6203					
GREASE	POLYREX EM							
INV.TYPE		**C HP FR**	60	**C HP TO**	90			
CT HZ FROM	6	**CT HZ TO**	60	**VT HZ FROM**	6	**VT HZ TO**	60	
SER.NO								
	SFA 6.26/3.13							

AC Induction Motor Performance Data
Record # 87157
Typical performance - not guaranteed values

Winding: 35WGG073-R001	**Type:** 3528M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			2	**Full Load Torque**	5.99 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			5.6/2.8	**Breakdown Torque**	20.5 LB-FT
R.P.M.			1760	**Pull-up Torque**	13.8 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	15 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	22.5 A
Service Factor (S.F.)			1.15	**No-load Current**	1.62 A
NEMA Nom. Eff.	86.5	**Power Factor**	77	**Line-line Res. @ 25ºC**	9.54 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	64°C
S.F. Amps			6.3/3.15	**Temp. Rise @ S.F. Load**	77°C
				Locked-rotor Power Factor	57.9
				Rotor inertia	0.202 lb-ft²

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	35	55	68	76	81	84	80
Efficiency	78.3	85.3	86.9	86.5	85.3	83.6	86.1
Speed	1791	1782	1771	1760	1748	1734	1754
Line amperes	1.71	1.97	2.34	2.82	3.36	3.97	3.13


ABB Motors and Mechanical Inc.

WINDING # 35WGG073


2 HP 3 PH 60 HZ 1760 RPM 460 V 3528M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=20.5 PU=13.8 LR=15 LRA=22.5




11/19/2026 ACPERF, record # 87157


35LYE4312
510-520 = 12.23
521-528 = 13.29
529-535 = 14.10
536-546 = 15.48
2.06
.13
1.88
Ø7.19
NAMEPLATE
.19 KEY
1.38 LONG
Ø6.50
Ø4.500
4.497
Ø.6250
.6245
3.81
SEE SPL INSTRUCTIONS ON PRODUCT SPEC FOR DRAIN AND PLUG LOCATIONS FOR BOTH ENDS.
6.61
5.37
4.55
45°
45°
THERMAL (WHEN REQ'D)
LEAD HOLE .50 N.P.T.
4 HOLES .38-16 TAP ON Ø5.88 B.C.
4.25
APPLY COAT OF SEALER UNDER BRG RET SCREW HEADS
FRONT END DETAIL
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE DRAIN AND DRAIN PLUG ORIENTATION
REV: C
VERSION: 03
REVISED: 02:08:39 05/29/2024
TDR: 000001233333
MODEL NO. 35LYE4312
REF: -
BY: USFRHAR
B
BALDOR - RELIANCE®
STD VER 56C TEFC 35M DDP (S/P032-002-002)
SH 1 of 1
35LYE4312

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS