ABB BALDOR RELIANCE

Customer information packet

VEFWDM3546T

1HP, 1770RPM, 3PH, 60HZ, 143TC, 3520M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/9/2026 6:26:27 PM

Specifications

Enclosure	TEFC
Frame	143TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.200 A @ 230.0 V
	3.200 A @ 208.0 V
	1.600 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	F
Type	AC
Mech. spec.	35SS605
Base	
Status	PRD/A
Elec. spec.	35WGG004
Layout	35LYSS605
Eff. date	06-05-2025
CD Diagram	CD0005
Poles	04
Leads	9#18,0# Y
Proprietary	False
Created date	01-10-2022

Heater Indicator	No Heater
High Voltage Full Load Amps	1.6 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3520M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.28 IN
Power Factor	69
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	VEFWDM3546T								
SPEC.	35SS605G004G1								
HP	1								
VOLTS	230/460								
AMP	3.2/1.6								
RPM	1770								
FRAME	143TC	**HZ**	60			**PH**	3		
SER.F.	1.15	**CODE**	N	**DES**	B	**CLASS**	F		
NEMA-NOM-EFF	85.5	**PF**	69						
RATING	40C AMB-CONT								
CC	010A								
DE	6205	**ODE**	6203						
ENCL	TEFC	**SN**							
BLANK	SFA 3.4/1.7								

AC Induction Motor Performance Data
Record # 91625
Typical performance - not guaranteed values

Winding: 35WGG004-R001	**Type:** 3520M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1	**Full Load Torque**	2.982 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			3.2/1.6	**Breakdown Torque**	14.6 LB-FT
R.P.M.			1770	**Pull-up Torque**	7.57 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	9.17 LB-FT
NEMA Design Code	B	**KVA Code**	N	**Starting Current**	14.6 A
Service Factor (S.F.)			1.15	**No-load Current**	1.2 A
NEMA Nom. Eff.	85.5	**Power Factor**	69	**Line-line Res. @ 25ºC**	16.049 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	36°C
S.F. Amps			3.4/1.7	**Temp. Rise @ S.F. Load**	41°C
				Locked-rotor Power Factor	61.549
				Rotor inertia	0.144 lb-ft²

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	29	45	58	67	73	78	71
Efficiency	71.1	81.2	84.7	85.8	86	85.6	85.9
Speed	1794	1787.3	1781.1	1774.3	1767.4	1759.4	1770
Line amperes	1.22	1.31	1.46	1.64	1.86	2.11	1.77


ABB Motors and Mechanical Inc.

WINDING # 35WGG004


1 HP 3 PH 60 HZ 1770 RPM 460 V 3520M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=14.6 PU=7.57 LR=9.17 LRA=14.6




11/9/2026 ACPERF, record # 91625


35LYSS605
510-520 = 12.28
521-528 = 13.29
529-535 = 14.16
536-546 = 15.53
2.12
.13
.13
FORSHEDA
SLINGER
(EACH END)
.19 KEY
1.38 LONG
Ø7.19
NAMEPLATE
Ø 4.500
4.497
Ø6.49
Ø .8750
.8745
(4) .125 NPT HOLES
3 w/PLUGS
@ 3, 9, & 1:00
(4) .125 NPT HOLES
3 w/PLUGS
@ 3, 9, & 11:00
3.76
6.61
5.77
45°
45°
4 HOLES
.38-16 TAP ON
5.88 DIA. B.C.
LEAD HOLE
.75 NPT
4.69
OMIT LOCK-WASHERS &
APPLY SEALER UNDER
BEARING RETAINER SCREW
HEADS & HOUSING O.D.
BEFORE PRESSING IN SEAL
FRONT END DETAIL
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE 3D MODEL BOM PER REV L, NO CHG TO 2D PRINT
REV: F
VERSION: 06
REVISED: 08:35:49 03/28/2022
TDR: 000001187751
MODEL NO. 35LYSS605
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
VERT 143-5TC TEFC 35M WD (S/P 9) W/.75 NPT LEAD HOLE
SH 1 of 1
35LYSS605

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS