

ABB BALDOR RELIANCE III

Customer information packet

VEL11318A

1HP, 1750RPM, 1PH, 60HZ, 56C, 3528LC, OPEN, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	1.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.400 A @ 230.0 V 8.800 A @ 115.0 V
Design Code	L
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	4.4 a
Insulation Class	F
Inverter Code	Not Inverter

Part Detail

Revision	G
Type	AC
Mech. spec.	35H993
Base	
Status	PRD/A
Elec. spec.	35WGG290
Layout	35LYH993
Eff. date	02-12-2026
CD Diagram	CD0703
Poles	04
Leads	7#16
Proprietary	False
Created date	11-03-2022

IP Rating	NONE
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	7 @ 16 AWG
Motor Lead Termination	None
Motor Standards	NEMA
Motor Type	3528LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.74 IN
Power Factor	89
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	SB
Winding Thermal 2	None

Nameplate

NP3273L											
CAT.NO.	VEL11318A										
SPEC.	35H993G290G1										
HP	1										
VOLTS	115/230										
AMP	8.8/4.4										
RPM	1750										
FRAME	56C		HZ	60				PH	1		
SER.F.	1.15	CODE	K	DES	L	CL	F				
F.L. AVG. EFF.	82.6	PF	89								
RATING	40C AMB-CONT										
CC											
DE	6205		ODE	6203							
ENCL	OPEN	SN									

AC Induction Motor Performance Data

Record # 91105

Preliminary Data Sheet

Winding: 35WGG290-R002				Type: 3528LC		Enclosure: OPEN		
Nameplate Data				115 V, 60 Hz: Low Voltage Connection				
Rated Output (HP)		1		Full Load Torque		3 LB-FT		
Volts		115/230		Start Configuration		direct on line		
Full Load Amps		8.8/4.4		Breakdown Torque		9.32 LB-FT		
R.P.M.		1750		Pull-up Torque		7.38 LB-FT		
Hz	60	Phase	1	Locked-rotor Torque		13.1 LB-FT		
NEMA Design Code		L	KVA Code	K		Starting Current		75.8 A
Service Factor (S.F.)		1.15		No-load Current		3.67 A		
NEMA Nom. Eff.		82.6	Power Factor	89	Line-line Res. @ 25°C		0.566 Ω A Ph 1.17 Ω B Ph	
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load		27°C
S.F. Amps						Temp. Rise @ S.F. Load		32°C
						Locked-rotor Power Factor		95.9
						Rotor inertia		0.203 lb-ft²

Load Characteristics 115 V, 60 Hz, 1 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	59	76	85	89	92	92	91
Efficiency	66.6	79.4	82.9	83.5	82.4	79.8	82.8
Speed	1786	1775	1763	1749	1734	1712	1740
Line amperes	4.17	5.38	6.91	8.7	10.7	13.3	9.9


ABB Motors and Mechanical Inc.


WINDING # 35WGG290

Typical performance - not guaranteed values.


1 HP 1 PH 60 HZ 1750 RPM 115 V 3528LC

TORQUES (LB-FT) : PO=9.32 PU=7.38 LR=13.1 LRA=75.8





CD0703



NOTES:

1. CONNECT LINE LEADS TO L1 AND L2.
LOW VOLTAGE: CONNECT AS SHOWN.
HIGH VOLTAGE: MOVE LEAD J TO TERM. 3.
MOVE LEAD 2 TO TERM. 4.
2. CONNECTIONS ARE SHOWN FOR STANDARD
ROTATION (CCW FACING END OPPOSITE
SHAFT EXTENSION). INTERCHANGE
LEADS 5 AND 8 TO REVERSE ROTATION.
3. MULTIPLE CAPACITORS ARE CONNECTED IN
PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST
ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REMOVE MODEL 17 CONNECTION

REV. LTR: G

VERSION: 02

TDR: 000001218314

FILE: \AAA\00007\140

REVISED: 08:28:11 10/11/2023

BY: ENBRIRO

MTL: —



BALDOR - RELIANCE®

TYPE LC, DV, REV, THERMAL, TERMINAL PLATE

SH 1 of 1

CD0703