

ABB BALDOR RELIANCE III

Customer information packet

VESSWDM3559T

3HP, 3470RPM, 3PH, 60HZ, 145TC, 3546M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	145TC
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.700 A @ 460.0 V 7.400 A @ 230.0 V 7.700 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	3.7 a
Insulation Class	F

Part Detail

Revision	E
Type	AC
Mech. spec.	35VV821
Base	
Status	PRD/A
Elec. spec.	35WGR930
Layout	35LYVV821
Eff. date	06-14-2024
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	07-05-2018

Inverter Code	Inverter Ready
KVA Code	P
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Finish	UNPAINTED
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3546M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	15.67 IN
Power Factor	91
Product Family	Wash Down All Stainless Steel
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3470 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1953A01											
CAT.NO.	VESSWDM3559T										
SPEC.	35VV821R930G1										
HP	3										
VOLTS	208-230/460										
AMP	7.7-7.4/3.7										
RPM	3470										
FRAME	145TC			HZ	60				PH	3	
SER.F.	1.15		CODE	P	DES	A		CLASS	F		
NEMA-NOM-EFF	86.5		PF	91							
RATING	40C AMB-CONT										
CC	010A										
DE	6205		ODE	6203							
ENCL	TEFC	SN									
	4:1CT 20:1VT										

AC Induction Motor Performance Data

Record # 35682

Typical performance - not guaranteed values

Winding: 35WGR930-R006			Type: 3546M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		3	Full Load Torque		4.5 LB-FT		
Volts		208-230/460	Start Configuration		direct on line		
Full Load Amps		7.7-7.4/3.7	Breakdown Torque		17.2 LB-FT		
R.P.M.		3470	Pull-up Torque		10.5 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		17 LB-FT	
NEMA Design Code		A	KVA Code	P	Starting Current		48.3 A
Service Factor (S.F.)		1.15	No-load Current		1.25 A		
NEMA Nom. Eff.		86.5	Power Factor	91	Line-line Res. @ 25°C		3.48 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		63°C
S.F. Amps					Temp. Rise @ S.F. Load		74°C
					Locked-rotor Power Factor		42
					Rotor inertia		0.127 LB-FT2

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	59	79	87	90	91	90	91
Efficiency	80.1	86.4	87.3	86.9	85.7	83.9	86.2
Speed	3567	3541	3510	3479	3443	3403	3457
Line amperes	1.53	2.07	2.78	3.55	4.42	5.4	4.07

ABB Motors and Mechanical Inc.

WINDING # 35WGR930

Typical performance - not guaranteed values.

3 HP 3 PH 60 HZ 3470 RPM 460 V 3546M

TORQUES (LB-FT): PO=17.2 PU=10.5 LR=17 LRA=48.3





