ABB BALDOR RELIANCE

Customer information packet

VEUHM3710T

7.5HP, 1770RPM, 3PH, 60HZ, 213TC, 3738M, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
9/9/2026 3:32:52 PM

Specifications

Enclosure	TEFC
Frame	213TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CE
	CSA
	CSA EEV
	NEMA PREMIUM
	UR
	WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	9.500 A @ 460.0 V
	20.000 A @ 208.0 V
	19.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	H
Type	AC
Mech. spec.	37A003
Base	
Status	PRD/A
Elec. spec.	37WGL864
Layout	37LYA003
Eff. date	05-01-2026
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	02-02-2021

Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	9.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3738M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.76 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2934L											
CAT.NO.	VEUHM3710T										
SPEC.	37A003L864G2										
HP	7.5/5.6KW										
VOLTS	230/460										
AMP	19/9.5										
R.P.M. (1/MIN)	1770										
FRAME	213TC	**HZ**	60	**PH**	3						
SER.F.	1.15	**CODE**	J	**DES**	A	**CL**	F				
NEMA-NOM-EFF	91.7	**PF**	80								
RATING	40C AMB-S1 CONT										
CC	010A	IP44 IC411 59KG									
DE	6307	**ODE**	6206								
ENCL	TEFC	**SN**									
	IE3-92.0(75%)91.4(50%)										

AC Induction Motor Performance Data
Record # 85467
Preliminary Data Sheet

Winding: 37WGL864-R001	**Type:** 3738M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			7.5	**Full Load Torque**	22.2 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			19.0/9.5	**Breakdown Torque**	69.8 LB-FT
R.P.M.			1770	**Pull-up Torque**	31.5 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	41 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	70.7 A
Service Factor (S.F.)			1.15	**No-load Current**	4.32 A
NEMA Nom. Eff.	91.7	**Power Factor**	80	**Line-line Res. @ 25ºC**	1.48 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	64°C
S.F. Amps			21.4/10.7	**Temp. Rise @ S.F. Load**	84°C
				Locked-rotor Power Factor	41.9
				Rotor inertia	0.934 lb-ft²

Load Characteristics 460 V, 60 Hz, 7.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	42	64	75	80	83	84	83
Efficiency	87.1	91.4	92	91.7	90.7	89.6	90.7
Speed	1793	1786	1778	1770	1760	1750	1761
Line amperes	4.83	6.03	7.64	9.5	11.6	13.9	10.7

ABB Motors and Mechanical Inc.

WINDING # 37WGL864

7.5 HP 3 PH 60 HZ 1770 RPM 460 V 3738M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=69.8 PU=31.5 LR=41 LRA=70.7




37LYA003
(717-720) = 17.00
(721-735) = 18.63
(736-744) = 19.75
(745-750) = 20.50
(751-756) = 21.25
5.01
3.12
.26
.31 KEY
2.38 LONG
Ø10.28
NAMEPLATE
9.06
Ø 1.3750
1.3745
Ø .002
-.001
9.64
7.93
45°
45°
7.17
LEAD HOLE
Ø1.38
6.69
4 HOLES
.50-13 TAP
ON Ø7.25 B.C.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: REMOVE GREASE CALLOUT
REV: J
VERSION: 02
REVISED: 10:54:43 04/14/2026
TDR: 000001275027
MODEL NO. 37LYA003
REF: -
BY: USTRTAY1
B
BALDOR
STD FACE MTD VERT 213-5TC TEFC 37M
37LYA003

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS