

ABB BALDOR RELIANCE III

Customer information packet

VHECP3660T

3HP, 3500RPM, 3PH, 60HZ, 182, HP, 0623M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	182HP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	7.000 A @ 230.0 V 7.520 A @ 208.0 V 3.500 A @ 460.0 V
Design Code	A
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	Y
Type	AC
Mech. spec.	06F448
Base	
Status	PRD/A
Elec. spec.	06WGW727
Layout	06LYF448
Eff. date	05-02-2023
CD Diagram	CD0005
Poles	02
Leads	9#16
Proprietary	False
Created date	10-31-2005

Heater Indicator	No Heater
High Voltage Full Load Amps	3.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	M
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0624M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	22.18 IN
Power Factor	89
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Face Code	P-Base
Pulley Shaft Indicator	P-Base Groove & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3510 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1260									
CAT.NO.	VHECP3660T								
SPEC.	06F448W727								
HP	3								
VOLTS	230/460								
AMP	7/3.5								
RPM	3510								
FRAME	182HP		HZ	60		PH		3	
SER.F.	1.15		CODE	M		DES	A	CL	F
NEMA-NOM-EFF	89.5		PF	89					
RATING	40C AMB-CONT								
CC	010A								
DE	6307		ODE		6206				
ENCL	TEFC		SN						

AC Induction Motor Performance Data

Record # 18074

Typical performance - not guaranteed values

Winding: 06WGW727-R001			Type: 0624M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		3	Full Load Torque		4.47 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		7/3.5	Breakdown Torque		25.3 LB-FT		
R.P.M.		3510	Pull-up Torque		16.2 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		18.4 LB-FT	
NEMA Design Code		A	KVA Code	M	Starting Current		39.3 A
Service Factor (S.F.)		1.15		No-load Current		1.4 A	
NEMA Nom. Eff.		89.5	Power Factor	89	Line-line Res. @ 25°C		3.26 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		35°C	
S.F. Amps				Temp. Rise @ S.F. Load		41°C	
				Locked-rotor Power Factor		46.1	
				Rotor inertia		0.107 LB-FT2	

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	51	72	84	89	91	92	90
Efficiency	80.8	87.7	89.6	89.7	89.2	88.5	89.4
Speed	3577	3556	3534	3510	3486	3458	3496
Line amperes	1.66	2.2	2.8	3.52	4.3	5.18	3.99

ABB Motors and Mechanical Inc.

WINDING # 06WGW727

Typical performance - not guaranteed values.

3 HP 3 PH 60 HZ 3510 RPM 460 V 0624M

TORQUES (LB-FT): PO=25.3 PU=16.2 LR=18.4 LRA=39.3





