ABB BALDOR RELIANCE

Customer information packet

VHECP4114T

52M 2P TEFC VER 326HP 32-6 SE DRIPCOVER
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/3/2026 2:24:19 AM

Specifications

Enclosure	TEFC
Frame	326HP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	UR
	CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	56.000 A @ 460.0 V
	122.000 A @ 208.0 V
	112.000 A @ 230.0 V
Design Code	A
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	J
Type	AC
Mech. spec.	12S033
Base	
Status	PRD/A
Elec. spec.	12WGY291
Layout	12LYS033
Eff. date	12-09-2025
CD Diagram	CD0180
Poles	02
Leads	9#8
Proprietary	False
Created date	05-29-2018

High Voltage Full Load Amps	56.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1252M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	34.72 IN
Power Factor	90
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Shaft Indicator	P-Base Groove & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3540 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1260									
CAT.NO.	VHECP4114T								
SPEC.	12S033Y291G1								
HP	50								
VOLTS	230/460								
AMP	112/56								
RPM	3540								
FRAME	326HP	**HZ**	60		**PH**	3			
SER.F.	1.15	**CODE**	H	**DES**	A		**CL**	F	
NEMA-NOM-EFF	93	**PF**	90						
RATING	40C AMB-CONT								
CC	010A								
DE	6312	**ODE**	6311						
ENCL	TEFC	**SN**							

AC Induction Motor Performance Data
Record # 31649
Typical performance - not guaranteed values

Winding: 12WGY291-R001	**Type:** 1252M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			50	**Full Load Torque**	74.4 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			112/56	**Breakdown Torque**	292 LB-FT
R.P.M.			3540	**Pull-up Torque**	112 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	139 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	408 A
Service Factor (S.F.)			1.15	**No-load Current**	14.9 A
NEMA Nom. Eff.	93	**Power Factor**	90	**Line-line Res. @ 25ºC**	0.11257 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	77°C
S.F. Amps				**Temp. Rise @ S.F. Load**	95°C
				Locked-rotor Power Factor	20.9
				Rotor inertia	4.07 LB-FT2

Load Characteristics 460 V, 60 Hz, 50 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	66	82	88	90	91	90	91
Efficiency	91.1	93.8	94.2	93.9	93.2	92.3	93.5
Speed	3584.1	3571.8	3558.2	3544.1	3528.2	3511.2	3535
Line amperes	20.4	30.8	42.9	55.8	69.5	84.6	64


ABB Motors and Mechanical Inc.


WINDING # 12WGY291

50 HP 3 PH 60 HZ 3540 RPM 460 V 1252M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=292 PU=112 LR=139 LRA=408





12LYS033
(1232-1272) = 34.72
13.67
4.531
4.469
4.02
GREASER
& RELIEF
(EA. END)
1.01
.25
.38 KEY
3.75 LONG
Ø16.77
.750
.745
.377
.375
13.505
13.500
16.49
MAX.
1.250
1.245
Ø1.6250
1.6245
LABEL
LB1182
.50-13 TAP
GND LOC.
17.43
13.76
8.50
45°
45°
3.00
DRAIN
HOLES
326 DRILL
(DRAIN)
LEAD HOLE
Ø2.00 NPT
11.33
4 HOLES
Ø.69 THRU
Ø14.750 B.C.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT DRW FROM AUTOCAD TO SWD
REV: H
VERSION: 06
REVISED: 10:52:47 11/17/2023
TDR: 000001220227
MODEL NO. 12LYS033
REF: -
BY: USALMAZ
B
BALDOR
VER TEFC 324-6HP ECP; 312 PU BRG
12LYS033

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1