

BALDOR • RELIANCE

Customer information packet

VL1317A

2HP, 3450RPM, 1PH, 60HZ, 56C, 3528L, OPEN, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	2.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 115.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	26.000 A @ 115.0 V 13.000 A @ 230.0 V
Design Code	L
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	70.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Terminal Panel
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	13.0 a

Part detail

Revision	BJ
Type	AC
Mech. spec.	35E523
Base	
Status	PRD/A
Elec. spec.	35WGW183
Layout	35LYE523
Eff. date	05-09-2024
CD Diagram	CD0052
Poles	02
Leads	4#14 A&J,2#18 B PH,1#10 #1TH
Proprietary	False
Created date	06-21-2007

Insulation Class	B
Inverter Code	Not Inverter
KVA Code	G
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Terminal Panel
Motor Lead Quantity/Wire Size	4 @ 14 AWG, A&J
Motor Lead Termination	None
Motor Standards	NEMA
Motor Type	3528L
Mounting Arrangement	F1
Number of Poles	2
Overall Length	12.74 IN
Power Factor	69
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.20
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible: Connected OPP STD
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Do Not Use Eve-Not Valid
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	SB

Winding Thermal 2

None

Nameplate

NP1257L									
CAT.NO.	VL1317A								
SPEC.	35E523W183								
HP	2								
VOLTS	115/230								
AMP	26/13								
RPM	3450								
FRAME	56C			HZ	60		PH	1	
SER.F.	1.20	CODE	G	DES	L	CL	B		
NEMA-NOM-EFF	70	PF	69						
RATING	40C AMB-CONT								
CC									
DE	6205	ODE	6203						
ENCL	OPEN	SN							
	SFA 27.6/13.8								

AC Induction Motor Performance Data

Record # 9776

Typical performance - not guaranteed values

Winding: 35WGW183-R001		Type: 3528L		Enclosure: OPEN	
Nameplate Data			230 V, 60 Hz: High Voltage Connection		
Rated Output (HP)	2		Full Load Torque	3 LB-FT	
Volts	115/230		Start Configuration	direct on line	
Full Load Amps	26/13		Breakdown Torque	10.4 LB-FT	
R.P.M.	3450		Pull-up Torque	5.9 LB-FT	
Hz	60 Phase	1	Locked-rotor Torque	7.1 LB-FT	
NEMA Design Code	L	KVA Code	G	Starting Current	79 A
Service Factor (S.F.)	1.2		No-load Current	9.3 A	
NEMA Nom. Eff.	70	Power Factor	69	Line-line Res. @ 25°C	0.842 Ω A Ph 0.843 Ω B Ph
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	77°C	
S.F. Amps	27.6/13.8		Temp. Rise @ S.F. Load	87°C	

Load Characteristics 230 V, 60 Hz, 2 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	38	53	65	71	80	84	78
Efficiency	46	60	66	70	68	67.5	68.4
Speed	3569	3547	3523	3498	3469	3436	3475
Line amperes	9.5	10.3	11.4	13	14.7	16.8	13.8


ABB Motors and Mechanical Inc.

WINDING # 35WGW183


Typical performance - not guaranteed values.

2 HP 1 PH 60 HZ 3450 RPM 230 V 3528L


TORQUES (LB-FT): PO=10.4 PU=5.9 LR=7.1 LRA=79



8/10/2024 ACPERF, record # 9776



CD0052



REV. DESC: REMOVE OPTIONAL THERMAL CONNECTION		
REV. LTR: H	VERSION: 01	TDR: 000000373039
CD0052	FILE: \AAA\00007\100	REVISED: 10:20:46 08/11/2005
	MTL: -	BY: ENJOEPO

BALDOR ELECTRIC Co.

TYPE L, DV, REV, THERMAL, TERMINAL PLATE

CD0052