

ABB BALDOR RELIANCE III

Customer information packet

VL3514T

1.5HP, 1725RPM, 1PH, 60HZ, 145TC, 3532LC, TEFC

Class - None

Division - Not Applicable

Specifications

| | |
|---------------------------------------|---|
| Enclosure | TEFC |
| Frame | 145TC |
| Frame Material | Steel |
| Frequency | 60.00 Hz |
| Haz Area Class and Group | None |
| Haz Area Division | Not Applicable |
| Motor Letter Type | Cap Start, Cap Run |
| Output @ Frequency | 1.500 HP @ 60 HZ |
| Phase | 1 |
| Synchronous Speed @ Frequency | 1800 RPM @ 60 HZ |
| Voltage @ Frequency | 115.0 V @ 60 HZ 230.0 V @ 60 HZ |
| Agency Approvals | C UR US |
| Ambient Temperature | 40 °C |
| Auxiliary Box | NO AUXILLARY BOX |
| Auxiliary Box Lead Termination | None |
| Base Indicator | No Mounting |
| Bearing Grease Type | Polyrex EM (-20F +300F) |
| Blower | None |
| Current @ Voltage | 12.200 A @ 115.0 V 6.100 A @ 230.0 V |
| Design Code | L |
| Drip Cover | No Drip Cover |
| Duty Rating | CONT |
| Efficiency @ 100% Load | 80.0 % |
| Electrically Isolated Bearing | Not Electrically Isolated |
| Feedback Device | NO FEEDBACK |
| Front Shaft Indicator | None |
| Heater Indicator | No Heater |
| High Voltage Full Load Amps | 6.1 a |
| Insulation Class | F |
| Inverter Code | Not Inverter |

Part Detail

| | |
|---------------------|------------|
| Revision | M |
| Type | AC |
| Mech. spec. | 35EE006 |
| Base | |
| Status | PRD/A |
| Elec. spec. | 35WGG242 |
| Layout | 35LYEE006 |
| Eff. date | 05-20-2025 |
| CD Diagram | CD0055 |
| Poles | 04 |
| Leads | 6#18 |
| Proprietary | False |
| Created date | 08-01-2022 |

| | |
|--------------------------------------|---------------------|
| KVA Code | H |
| Lifting Lugs | No Lifting Lugs |
| Locked Bearing Indicator | Locked Bearing |
| Motor Lead Quantity/Wire Size | 6 @ 18 AWG |
| Motor Lead Termination | Flying Leads |
| Motor Standards | NEMA |
| Motor Type | 3532LC |
| Mounting Arrangement | F1 |
| Number of Poles | 4 |
| Overall Length | 14.17 IN |
| Power Factor | 98 |
| Product Family | General Purpose |
| Pulley End Bearing Type | Ball |
| Pulley Face Code | C-Face |
| Pulley Shaft Indicator | Standard |
| Rodent Screen | None |
| Service Factor | 1.15 |
| Shaft Diameter | 0.875 IN |
| Shaft Ground Indicator | No Shaft Grounding |
| Shaft Rotation | Reversible |
| Shaft Slinger Indicator | No Slinger |
| Speed | 1725 rpm |
| Speed Code | Single Speed |
| Starting Method | Direct on line |
| Thermal Device - Bearing | None |
| Thermal Device - Winding | None |
| Vibration Sensor Indicator | No Vibration Sensor |
| Winding Thermal 1 | None |
| Winding Thermal 2 | None |

Nameplate

| NP1256L | | | | | | | | | | |
|---------------------|--------------|-------------|------------|------------|---|--------------|-----------|---|--|--|
| CAT.NO. | VL3514T | | | | | | | | | |
| SPEC. | 35EE006G242 | | | | | | | | | |
| HP | 1.5 | | | | | | | | | |
| VOLTS | 115/230 | | | | | | | | | |
| AMP | 12.2/6.1 | | | | | | | | | |
| RPM | 1725 | | | | | | | | | |
| FRAME | 145TC | | HZ | 60 | | | PH | 1 | | |
| SER.F. | 1.15 | CODE | H | DES | L | CLASS | F | | | |
| NEMA-NOM-EFF | 80 | PF | 98 | | | | | | | |
| RATING | 40C AMB-CONT | | | | | | | | | |
| CC | | | | | | | | | | |
| DE | 6205 | | ODE | 6203 | | | | | | |
| ENCL | TEFC | SN | | | | | | | | |


ABB Motors and Mechanical Inc.


WINDING # 35WGG242

Typical performance - not guaranteed values.


1.5 HP 1 PH 60 HZ 1725 RPM 115 V 3532LC

TORQUES (LB-FT): PO=9.9 PU=8.1 LR=13 LRA=88





CD0055



| | LINE A | LINE B | JOIN |
|----------|--------|--------|-------|
| HIGH STD | 1 | 4,5 | 2,3,8 |
| HIGH OPP | 1 | 4,8 | 2,3,5 |
| LOW STD | 1,3,8 | 2,4,5 | - |
| LOW OPP | 1,3,5 | 2,4,8 | - |

- NOTES:
1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
 2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
 3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0055

| | | | |
|---|---------|------------------------|--------------|
| REV. DESC: REVISE TO SHOW OPTIONAL COLORS | | | |
| REV. LTR: D | BY: JLP | REVISED: 04/08/99 1:17 | TDR: 0178636 |
| C00000 | | FILE: AAA00007414 | MDL: - |
| | | MTL: - | |

BALDOR ELECTRIC Co.

TYPE LC, DV, REV, 6 LEADS