

ABB BALDOR RELIANCE III

Customer information packet

VLECP3774T

10HP, 1760RPM, 3PH, 60HZ, 215LP, 0748M, TEFC, F

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	215LP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CCSA US CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.3
Current @ Voltage	25.000 A @ 230.0 V 12.500 A @ 460.0 V
Design Code	A
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	841
Feedback Device	NO FEEDBACK

Part Detail

Revision	N
Type	AC
Mech. spec.	07H347
Base	
Status	PRD/A
Elec. spec.	07WGX776
Layout	07LYH347
Eff. date	09-22-2022
CD Diagram	CD0005
Poles	04
Leads	9#14 Y
Proprietary	False
Created date	07-09-2015

Front Face Code	Drip Cover Mounting
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	12.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0748M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	22.51 IN
Power Factor	82
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Thrust
Pulley Face Code	P-Base
Pulley Shaft Indicator	P-Base Groove & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line

Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3258											
CAT.NO.	VLECP3774T										
SPEC.	07H347X776G1										
HP	10 TE										
VOLTS	230/460										
AMP	25/12.5										
RPM	1760										
FRAME	215LP	HZ	60		PH	3					
SER.F.	1.15	CODE	H	DES	A	CL	F				
RATING	40C AMB-CONT										
SN											
DE	QJ211	ODE	6307								
NEMA-NOM-EFF	92.4	PF	82								
G.MIN.EFF	91	CC	010A								
T. CODE	T3C	T=	160								

NP3261			
SPEC.	07H347X776G1		
D.E. BRG.	55BZ02X00X		
O.D.E. BRG.	35BC03X30X		
GREASE	POLYREX EM		
RPM MAX	2700	MAX. KVAR	1.7
BLANK			
INV.TYPE	PWM		
T=	160		
C HP FR	60	C HP TO	90
CT HZ FROM	1.3	CT HZ TO	60
VT HZ FROM	-0	VT HZ TO	60
HTR-VOLTS	N/A	HTR-AMPS	N/A
HTR-WATTS	N/A	MAX. SPACE HEATER TEMP.	N/A

AC Induction Motor Performance Data

Record # 25097

Typical performance - not guaranteed values

Winding: 07WGX776-R016				Type: 0748M		Enclosure: TEFC	
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		10		Full Load Torque		29.8 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		25/12.5		Breakdown Torque		87 LB-FT	
R.P.M.		1760		Pull-up Torque		51.9 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		57.5 LB-FT	
NEMA Design Code		A	KVA Code	Starting Current		88.5 A	
Service Factor (S.F.)		1.15		No-load Current		5.12 A	
NEMA Nom. Eff.		92.4	Power Factor	Line-line Res. @ 25°C		0.973 Ω	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		60°C	
S.F. Amps				Temp. Rise @ S.F. Load		76°C	
				Locked-rotor Power Factor		35	
				Rotor inertia		1.18 LB-FT2	

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	44	67	78	82	84	85	83
Efficiency	90	92.9	93.1	92.5	91.4	90.1	91.8
Speed	1790	1781	1771	1762	1750	1739	1755
Line amperes	5.84	7.52	9.75	12.3	15.2	18.3	14

ABB Motors and Mechanical Inc.

WINDING # 07WGX776

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 1760 RPM 460 V 0748M

TORQUES (LB-FT): PO=87 PU=51.9 LR=57.5 LRA=88.5





