ABB BALDOR RELIANCE

Customer information packet

VLECP4104T

30HP, 1760RPM, 3PH, 60HZ, 286LP, 1056M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 1:58:35 PM

Specifications

Enclosure	TEFC
Frame	286LP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.3
Current @ Voltage	78.000 A @ 208.0 V
	76.000 A @ 230.0 V
	38.000 A @ 460.0 V
Design Code	A
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	Q
Type	AC
Mech. spec.	10M69
Base	
Status	PRD/A
Elec. spec.	10WGY538
Layout	10LYM069
Eff. date	06-05-2026
CD Diagram	CD0180
Poles	04
Leads	9#8
Proprietary	False
Created date	08-24-2017

Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	38.0 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	J
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1056M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	32.44 IN
Power Factor	80
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Thrust
Pulley Face Code	P-Base
Pulley Shaft Indicator	P-Base Groove & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.750 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	NONE (OLD)

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3241

CAT.NO.	VLECP4104T		**P/N**				**ENCLOSURE**	TEFC					
SPEC.	10M069Y538G1	**CC**	010A	**FRAME**	286LP		**S/N**						
HP	30		**CLASS**	F	**HZ**	60	**DES**	A					
RPM	1760		**RPM MAX**	2700	**PH**	3	**KVA-CODE**	J					
VOLT	230/460			**MOTOR WEIGHT**	549								
AMP	76/38		**SER.F.**	1.15	**PF**	80	**ODE BRG**	6309	**DE BRG**	QJ213			
RATING	40C AMB-CONT			**NEMA-NOM-EFF**	93.6		**GREASE**	POLYREX EM					
					INV.TYPE	PWM							
TEMP CODE	T3C		**INVERTER-TEMP-CODE**	180									
TEMP =	160	**C HP FR**	60		**C HP TO**	90							
CT HZ FROM	1.3		**CT HZ TO**	60									
HTR-VOLTS		**HTR-AMPS**		**HTR-WATTS**			**MAX. SPACE HEATER TEMP.**				**VT HZ FROM**	O	**VT HZ TO** 60

AC Induction Motor Performance Data
Record # 66469
Typical performance - not guaranteed values

Winding: 10WGY538-R042	**Type:** 1056M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			30	**Full Load Torque**	88.7 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			76/38	**Breakdown Torque**	330 LB-FT
R.P.M.			1760	**Pull-up Torque**	142 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	178 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	270 A
Service Factor (S.F.)			1.15	**No-load Current**	17.9 A
NEMA Nom. Eff.	93.6	**Power Factor**	80	**Line-line Res. @ 25ºC**	0.19377 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	64°C
S.F. Amps				**Temp. Rise @ S.F. Load**	76°C
				Locked-rotor Power Factor	30.9
				Rotor inertia	4.47 LB-FT2

Load Characteristics 460 V, 60 Hz, 30 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	41	63	73	80	82	85	81
Efficiency	87.6	92.3	93.5	93.7	93.4	92.9	93.5
Speed	1792.2	1787.6	1782.4	1776.5	1770.3	1762.1	1773
Line amperes	19.8	24.3	30.7	37.6	45.6	55.2	42.4


ABB Motors and Mechanical Inc.


WINDING # 10WGY538

30 HP 3 PH 60 HZ 1760 RPM 460 V 1056M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=330 PU=142 LR=178 LRA=270





10LYM069
(1028-1060) = 32.44
19.46
15.45
4.50
.25
.67
4.00
.50 KEY
2.50 LONG
8.253
8.250
Ø9.87
2.1250
2.1240
Ø2.260
2.240
SLINGER
.38-16 TAP
GND LOC.
19.10
12.59
7.80
3.39
45°
45°
DRAIN
HOLE
.25
DRAIN
HOLE
LEAD HOLE
2.00 NPT
4 HOLES
Ø.44 ON
Ø9.12 B.C.
10.16
HW4600B43
3.78
KEYWAY
.750
.745
HW4600B42
.377
.375
2.1250
2.1240
1.750
1.745
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT DRW FROM AUTOCAD TO SWD
REV: P
VERSION: 09
REVISED: 02:15:30 11/10/2023
TDR: 000001220227
MODEL NO. 10LYM069
REF: -
BY: USALMAZ
B
BALDOR
VERT TEFC 284-6LP CP
10LYM069

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1