

ABB BALDOR RELIANCE III

Customer information packet

VM3606

1.5HP, 1755RPM, 3PH, 60HZ, 184C, 3521M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	184C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.100 A @ 208.0 V 4.800 A @ 230.0 V 2.400 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	K
Type	AC
Mech. spec.	35H324
Base	
Status	INA/A
Elec. spec.	35WGZ541
Layout	35LYH324
Eff. date	09-12-2017
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	04-29-2010

Heater Indicator	No Heater
High Voltage Full Load Amps	2.4 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	M
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3521M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.31 IN
Power Factor	70
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1755 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP1256L									
CAT.NO.									
SPEC.	35H324Z541H1								
HP	1.5								
VOLTS	208-230/460								
AMP	5.1-4.8/2.4								
RPM	1755								
FRAME	184C		HZ		60		PH		3
SER.F.	1.15	CODE		M	DES	B	CLASS		F
NEMA-NOM-EFF	84	PF		70					
RATING	40C AMB-CONT								
CC	010A								
DE	6205		ODE		6203				
ENCL	TEFC	SN							

AC Induction Motor Performance Data

Record # 23168

Typical performance - not guaranteed values

Winding: 35WGZ541-R001			Type: 3522M		Enclosure: TEFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		1.5	Full Load Torque		4.42 LB-FT	
Volts		208-230/460	Start Configuration		direct on line	
Full Load Amps		5.1-4.8/2.4	Breakdown Torque		19.8 LB-FT	
R.P.M.		1755	Pull-up Torque		10.65 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque		14 LB-FT	
NEMA Design Code		B KVA Code	Starting Current		19.38 A	
Service Factor (S.F.)		1.15	No-load Current		1.59 A	
NEMA Nom. Eff.		84 Power Factor	Line-line Res. @ 25°C		9.72 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		55°C	
S.F. Amps			Temp. Rise @ S.F. Load		63°C	
			Locked-rotor Power Factor		53.6	
			Rotor inertia		0.13 LB-FT2	

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	30	48	62	70	77	80	74
Efficiency	68.5	79.3	83.4	84.3	84.2	83.1	83.9
Speed	1792	1783	1773	1762	1751	1737	1754
Line amperes	1.64	1.8	2.04	2.35	2.7	3.11	2.57

ABB Motors and Mechanical Inc.

WINDING # 35WGZ541

Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 1755 RPM 460 V 3522M

TORQUES (LB-FT): PO=19.8 PU=10.65 LR=14 LRA=19.38



