

ABB BALDOR RELIANCE III

Customer information packet

VLECP84107T-4

48M 2P TEFC VER 284LP IEEE841 32-8 DRIP

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	284LP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM UR CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	28.000 A @ 460.0 V
Design Code	B
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	841
Feedback Device	NO FEEDBACK
Front Shaft Indicator	Standard
Haz Area Temp Code	T3

Part Detail

Revision	H
Type	AC
Mech. spec.	10K389
Base	
Status	PRD/A
Elec. spec.	10WGZ242
Layout	10LYK389
Eff. date	10-08-2025
CD Diagram	CD0006
Poles	02
Leads	3#10
Proprietary	False
Created date	03-25-2019

Heater Indicator	No Heater
High Voltage Full Load Amps	28.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP56
KVA Code	F
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Quantity/Wire Size	3 @ 10 AWG
Motor Lead Termination	Ring Terminals
Motor Standards	NEMA
Motor Type	1048M
Mounting Arrangement	V1
Number of Poles	2
Overall Length	36.31 IN
Power Factor	90
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley End Bearing Type	Ball
Pulley Face Code	P-Base
Pulley Shaft Indicator	P-Base Groove & Key
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3520 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate
NP4332

CAT.NO.	VLECP84107T-4			P/N		ENCLOSURE			TEFC				
SPEC.	10K389Z242G1			CC	010A	FRAME	284LP	S/N					
HP	25			CLASS	F	HZ	60	ODE BRG	7309	DE BRG	6213		
RPM	3520	RPM MAX	5400	PH	3	DES	B	D.E. BRG.	65BC02X30X				
VOLT	460			KVA-CODE	F		O.D.E. BRG.	45BT03X30X					
AMP	28			MOTOR WEIGHT			396	GREASE	POLYREX EM				
RATING	40C AMB-CONT			MAX. KVAR			3.1	BLANK					
NEMA-NOM-EFF	91.7	# OF ROTOR BARS			28	SER.F.	1.15	IP	56				
G.MIN.EFF	90.2	# OF STATOR SLOTS			36	PF	90	INV.TYPE	PWM				
TEMP CODE	T3	INVERTER-TEMP-CODE			200								
TEMP =	200	C HP FR	60	C HP TO	90								
CT HZ FROM	1.3	CT HZ TO	60										
HTR-VOLTS		HTR-AMPS		HTR-WATTS		MAX. SPACE HEATER TEMP.				VT HZ FROM	0-	VT HZ TO	60

AC Induction Motor Performance Data

Record # 47223

Typical performance - not guaranteed values

Winding: 10WGZ242-R004			Type: 1048M		Enclosure: TEFC	
Nameplate Data				460 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)		25		Full Load Torque		37.3 LB-FT
Volts		460		Start Configuration		direct on line
Full Load Amps		28		Breakdown Torque		103 LB-FT
R.P.M.		3520		Pull-up Torque		42.1 LB-FT
Hz	60	Phase	3	Locked-rotor Torque		54 LB-FT
NEMA Design Code		B	KVA Code	F	Starting Current	
Service Factor (S.F.)		1.15		No-load Current		6.99 A
NEMA Nom. Eff.		91.7	Power Factor	90	Line-line Res. @ 25°C	
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load
S.F. Amps						Temp. Rise @ S.F. Load
						Locked-rotor Power Factor

Load Characteristics 460 V, 60 Hz, 25 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	69	83	89	90	90	90	90
Efficiency	87.8	91.6	92.2	91.8	90.9	89.7	91.3
Speed	3580.1	3563.2	3542.7	3521.3	3497	3469.9	3507
Line amperes	10.1	15.4	21.7	28.3	35.7	43.5	32.7


ABB Motors and Mechanical Inc.

WINDING # 10WGZ242


Typical performance - not guaranteed values.

25 HP 3 PH 60 HZ 3520 RPM 460 V 1048M




TORQUES (LB-FT): PO=103 PU=42.1 LR=54 LRA=171



10/20/2026 ACPERF, record # 47223



CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10: 24: 49 02/19/2019

BY: ENBRIRO

MTL: -



BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1