

ABB BALDOR RELIANCE III

Customer information packet

VP3428D

.37/.50KW, 3000RPM, DC, D71D, 3416P, TEFC, F2

Class - None

Division -

Specifications

Armature Voltage	180 V
Base Speed	3000 rpm
Enclosure	TEFC
Frame	D71D
Frame Material	Steel
Haz Area Class and Group	None
Output Power	0.373 HP
Agency Approvals	CE CSA UR
Ambient Temperature	40 °C
Armature Current	2.5 a
Armature Inertia	6.243 lb-ft ²
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Frame Prefix	D
Heater Indicator	No Heater
Lifting Lugs	No Lifting Lugs
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	IEC
Mounting Arrangement	B35
Overall Length	13.15 IN
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	0.552 IN

Part Detail

Revision	AG
Type	DC
Mech. spec.	34-6173
Base	
Status	PRD/A
Elec. spec.	34WGZ132
Layout	34LY6173
Eff. date	10-25-2024
CD Diagram	CD0194
Poles	00
Leads	
Proprietary	False
Created date	01-01-0001

Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Nameplate

NP1049L				
CAT.NO.	VP3428D			
SPEC.	34-6173Z132			
KW/HP	.37/.50 TE		I.P.	54
RPM	3000 1/MIN IP411 15KG TE			
IEC FRAME	D71D	TYPE	3416P	
ARM V	180		ARM A	2.5
FLD V			FLD A	
INSUL	F	AMB.	40	
DUTY	CONT		SUPPLY	1.5
BRG/DE	6203	BRG/ODE		6203
BRUSHES	2/BP5000AW14			
			BLANK	
SER.				
BLANK				
APRV-CE	APRV-CSA	APRV-UL		

Accessories

Part number	Description	Multiplier
TK3400	TACHO MOUNTING KIT FOR TK3400	A8
TK3400-HPU	HPU10 MOUNTING KIT 34P/35P TEFC	

DC Motor Performance Data

Record # 1439

Typical performance - not guaranteed values

Winding: 34WGZ132-R003		Type: 3416P	Enclosure: TEFC
Nameplate Data		General Characteristics	
Rated Output (KW)	0.373	Armature Resistance @ 25°C	2.069 Ω
R.P.M.	3000		
Armature Volts	180		
Armature Amps	2.5		
Field Volts			
Field Amps			
Rating - Duty	40C AMB-CONT		
Form Factor	1.5		

Load Characteristics at 180 Armature Volts

Load Point	1	2	3	4	5	6
Armature Amps	0.3	1.6	2.2	2.9	3.5	4.2
R.P.M.	3262	3177	3144	3099	3064	3016
Torque (LB-FT)	0	0.516	0.752	1.01	1.246	1.504


ABB Motors and Mechanical Inc.


WINDING # 34WGZ132

Typical performance - not guaranteed values.


0.373 KW DC 3000 RPM 180 V 3416P

ENCL: TEFC DUTY: CONT CL: F





CD0194



NOTES:

1. CCW ROTATION AS SHOWN FACING COMMUTATOR END. TO REVERSE MOTOR ROTATION OR TACHOMETER OUTPUT POLARITY INTERCHANGE LEADS A1(RED) & A2(BLACK)
2. LEAD COLORS FOR REFERENCE ONLY & NOT SPECIFIED BY THIS DRAWING. LEAD COLORS SPECIFIED BY LAYOUT DRAWING & BILL OF MATERIAL ONLY.

MATL: -			
REV:	E	ADDED NOTE "LEAD COLORS FOR REFERENCE ONLY &..."	
CD0194		SCALE: -	BY: CK
		FILE: AAA00004503	TDR: 0078737

BALDOR ELECTRIC Co.

CD TYPE P DC PERMANENT MAGNET MOTORS AND TACHOMETERS

CD0194