

ABB BALDOR RELIANCE III

Customer information packet

VP3468-14

1.5HP/1.1KW/3000RPM/TEFC 34-6243Z178

Class - None

Division - Not Applicable

Specifications

Armature Voltage	180 V
Base Speed	3000 rpm
Enclosure	TEFC
Frame	D80C
Haz Area Class and Group	None
Output Power	1.500 HP
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Armature Current	7.7 a
Armature Inertia	12.486 lb-ft ²
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Frame Prefix	D
Haz Area Division	Not Applicable
Heater Indicator	No Heater
Insulation Class	F
Lifting Lugs	No Lifting Lugs
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	IEC
Mounting Arrangement	B34
Overall Length	15.22 IN
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Service Factor	1.00
Shaft Diameter	0.748 IN
Shaft Extension Location	Pulley End

Part Detail

Revision	AB
Type	DC
Mech. spec.	34-6243
Base	
Status	PRD/A
Elec. spec.	34WGZ178
Layout	34LY6243
Eff. date	10-25-2024
CD Diagram	CD0194
Poles	00
Leads	
Proprietary	False
Created date	01-01-0001

Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Nameplate

NP1049L					
CAT.NO.	VP3468-14				
SPEC.	34-6243Z178				
KW/HP	1.1/1.5 TE			I.P.	44
RPM	3000 1/MIN				
IEC FRAME	D80C	TYPE		3432P	
ARM V	180			ARM A	7.7
FLD V				FLD A	
INSUL	F	AMB.		40	
DUTY	CONT			SUPPLY	1.5
BRG/DE	6205	BRG/ODE		6203	
BRUSHES	2/BP5000AW14				
				BLANK	KG20 IC411
SER.					
BLANK	IEC60034-1;-5				
APRV-CE	Y	APRV-CSA	Y	APRV-UL	Y

Accessories

Part number	Description	Multiplier
TK3400	TACHO MOUNTING KIT FOR TK3400	A8
TK3400-HPU	HPU10 MOUNTING KIT 34P/35P TEFC	

DC Motor Performance Data

Record # 600

Typical performance - not guaranteed values

Winding: 34WGZ178-R001		Type: 3432P	Enclosure: TEFC
Nameplate Data		General Characteristics	
Rated Output (HP)	1.5	Armature Resistance @ 25°C	0.8865 Ω
R.P.M.	3000		
Armature Volts	180		
Armature Amps	7.7		
Field Volts		Armature Inductance	9.116 mH
Field Amps			
Rating - Duty	40C AMB-CONT		
Form Factor	1.5		

Load Characteristics at 180 Armature Volts

Load Point	1	2	3	4	5	6	7
Armature Amps	0.51	2.41	4.04	5.73	7.3	8.91	10.52
R.P.M.	3083	3018	2983	2934	2902	2855	2804
Torque (LB-FT)	0	0.66	1.32	1.97	2.63	3.29	3.95


ABB Motors and Mechanical Inc.


WINDING # 34WGZ178

Typical performance - not guaranteed values.


1.5 HP DC 3000 RPM 180 V 3432P

ENCL: TEFC DUTY: CONT CL: F





CD0194



NOTES:

1. CCW ROTATION AS SHOWN FACING COMMUTATOR END. TO REVERSE MOTOR ROTATION OR TACHOMETER OUTPUT POLARITY INTERCHANGE LEADS A1(RED) & A2(BLACK)
2. LEAD COLORS FOR REFERENCE ONLY & NOT SPECIFIED BY THIS DRAWING. LEAD COLORS SPECIFIED BY LAYOUT DRAWING & BILL OF MATERIAL ONLY.

MATL: -

REV: E

ADDED NOTE "LEAD COLORS FOR REFERENCE ONLY &..."

CD0194

SCALE: -

BY: CK

REVISED: 07/28/95

FILE: AAA00004503

TDR: 0078737

BALDOR ELECTRIC Co.

CD TYPE P DC PERMANENT MAGNET MOTORS AND TACHOMETERS

CD0194