

# DUTY MASTER ALTERNATING CURRENT MOTORS

617428-660

ENCLOSURE: TOTALLY ENCLOSED






SQUIRREL-CAGE INDUCTION

COOLING: FAN COOLED

MOUNTING: FOOTLESS, V-1

FRAME E365VP/E364VP

841-XL ENHANCEMENT



DIMENSIONS ARE IN INCHES.  
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

SHEET NUMBER  
**1 OF 1**  
617428-660

FACE RUNOUT & ECCENTRICITY RUNOUT = .004 T.I.R.  
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.  
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .001 T.I.R.

REV. DESC: NEW DRAWING			
REV: -	VERSION: 00	REVISED: 03:43:18 03/04/2019	TDR: 000001100681
MODEL NO. 617428-660			
BY: USJEDIL			

**BALDOR**

E365/364VP TEFC V1 FOOTLESS/CAST IRON CONDUIT BOX/INPROS

617428-660