

ABB BALDOR RELIANCE III

Customer information packet

VPECP84316T-4

75HP, 1780RPM, 3PH, 60HZ, 365VP, A36070M, TEFC

Class - None

Division - Division II

Specifications

Enclosure	TEFC
Frame	365VP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	75.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV CURUSEEV NEMA PREMIUM NEMA PREMIUM (OLD LOGO) UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	15-60
Current @ Voltage	86.000 A @ 460.0 V
Design Code	B
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.4 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	86.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G

Part Detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG3963
Layout	617428-660
Eff. date	03-13-2026
CD Diagram	416820-036
Poles	04
Leads	3#4
Proprietary	False
Created date	07-23-2025

Lifting Lugs	Vertical Lifting Lugs
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A36070M
Mounting Arrangement	V1
Number of Poles	4
Overall Length	37.27 IN
Power Factor	86
Product Family	Pump - Centrifugal
Pulley End Bearing Type	Ball
Pulley Face Code	P-Base
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP4388																	
CAT #	VPECP84316T-4						FR	365VP			56						
SPEC	A36-7900-3963						ENCL	TEFC			DES	B					
HZ	60	PH	3	CL	F	HP	75	SF	1.15	PF	86	%	CODE	G			
VOLTS	460					AMPS	86										
RPM	1780		MAX RPM		2700		SER										
NEMA NOM. EFF	95.4	%	RATING		40C AMB-CONT												
GUAR MIN. EFF	94.5	%	BRG DE		6313			BRG ODE		7310							
CL I DIV 2 GRPS A,B,C,D						CL I ZONE 2 GRPS				IIA,IIB,IIC			TEMP T		3-200	C	
CT HZ	15-60		VT HZ		0-60												
CHP HZ	60-90		INV TEMP CL					200	C								
								MTR WT		965	LBS						

NP4333									
	CAT #	VPECP84316T-4		ROTOR BARS		47			
	SPEC	A36-7900-3963		STATOR SLOTS		60			
	SER			MAX CORR KVAR		15.8			
	GREASE	POLYREX EM							
	ABMA DE BRG	65BC03JP30X	ODE	BA2B_459310					
SPACE HEATER LEADS H1-H2:		TIE LIKE NUMBERS				TOGETHER			
MAX. SPACE HEATER TEMP.			C	V		A		W	

AC Induction Motor performance data

Record #71698 - Typical performance - not guaranteed values

Winding	A36WG3963
Type	A3670M
Enclosure	TEFC

Nameplate data

Rated Output			75
Volts			460
Full Load Amps			86
R.P.M.			1780
Hz	60	Phase	3
KVA Code			F
S.F.			1.15
NEMA Nom. Eff.	95	Power Factor	86
Duty			CONT
S.F. Amps			

460 V. 60 Hz:

Single Voltage Motor


Full Load Torque	220.2 LB-FT
Start Configuration	direct on line
Breakdown Torque	542 LB-FT
Pull-up Torque	372 LB-FT
Locked-rotor Torque	445 LB-FT
Starting Current	541 A
No-load Current	27.9
Line-line Res. @ 25°C	0.082276 Ω
Temp. Rise @ Rated Load	55°C
Temp. Rise @ S.F. Load	69°C
Locked-rotor Power Factor	31.8
Rotor inertia	16.2 lb-ft ²


Load Characteristics 460 V, 60 Hz, 75 HP

% of Rated Load	NL	25	50	75	100	125	150	SF
Power Factor	3	54	75	83	85	86	85	86
Efficiency	0	94.1	95.9	95.9	95.5	94.9	93.8	95.1
Speed	1798.9	1796.2	1792.2	1788	1783.5	1778.5	1771.1	1780
Line amperes	27.9	34.1	48.5	66.3	85.9	108	136	99.2

75 HP 3 PH 60 HZ 1780 RPM 460 V A3670M


TORQUES (LB-FT): PO=542.00 PU=372.00 LR=445.00 LRA=541.00





416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682		REVISED: 11: 54: 06 04/30/2010
MTL: -		BY: RAGRA

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1