

ABB BALDOR RELIANCE III

Customer information packet

VP3326D

.37/.5HP, 1750RPM, DC, D71D, 3336P, TENV, F2

Part Detail


Revision	Y
Type	DC
Mech. spec.	33-2370
Base	
Status	PRD/A
Elec. spec.	33WGZ139
Layout	33LY2370
Eff. date	10-24-2024
CD Diagram	CD0194
Poles	00
Leads	2#18 A Y
Proprietary	False
Created date	01-01-0001

Nameplate


NP1049L					
CAT.NO.	VP3326D				
SPEC.	33-2370Z139				
KW/HP	.37/.5 TE			I.P.	54
RPM	1750 1/MIN				
IEC FRAME	D71D	TYPE		3336P	
ARM V	180			ARM A	2.5
FLD V				FLD A	
INSUL	F	AMB.		40	
DUTY	CONT			SUPPLY	1.3
BRG/DE	6203	BRG/ODE			6203
BRUSHES	2/BP5011CV01				
				BLANK	
SER.					
BLANK	IEC60034-1;-5 IC410 KG14				
APRV-CE	Y	APRV-CSA	Y	APRV-UL	Y

Accessories

Part number	Description	Multiplier
TK3300	TACHO MOUNTING KIT TK3300	A8
TK3300-HPU	HPU10 MOUNTING KIT 33P/34P TENV	



CD0194



NOTES:

1. CCW ROTATION AS SHOWN FACING COMMUTATOR END. TO REVERSE MOTOR ROTATION OR TACHOMETER OUTPUT POLARITY INTERCHANGE LEADS A1(RED) & A2(BLACK)
2. LEAD COLORS FOR REFERENCE ONLY & NOT SPECIFIED BY THIS DRAWING. LEAD COLORS SPECIFIED BY LAYOUT DRAWING & BILL OF MATERIAL ONLY.

MATL: -			
REV:	E	ADDED NOTE "LEAD COLORS FOR REFERENCE ONLY &..."	
CD0194		SCALE: -	BY: CK
		FILE: AAA00004503	TDR: 0078737

BALDOR ELECTRIC Co.

CD TYPE P DC PERMANENT MAGNET MOTORS AND TACHOMETERS

CD0194