



Customer information packet

VRBM3554T

1.5HP, 1710RPM, 3PH, 60HZ, 145TC, 7524M, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	145TC
Frame Material	Aluminum
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.600 A @ 208.0 V 4.300 A @ 230.0 V 2.150 A @ 460.0 V
Design Code	D
Duty Rating	CONT
Efficiency @ 100% Load	81.5 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	2.2 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	J
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Standards	NEMA

Part detail

Revision	D
Type	AC
Mech. spec.	75J035
Base	
Status	PRD/A
Elec. spec.	75WGW130
Layout	75LYJ035
Eff. date	05-14-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	03-11-2022

Motor Type	7524M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.40 IN
Power Factor	80
Product Family	General Purpose
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1710 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	VRBM3554T								
SPEC.	75J035W130G1								
HP	1.5								
VOLTS	230/460								
AMP	4.3/2.15								
RPM	1710								
FRAME	145TC		HZ	60		PH	3		
SER.F.	1.15	CODE	J	DES	D	CLASS	F		
NEMA-NOM-EFF	81.5	PF	80						
RATING	40C AMB-CONT								
CC									
DE	6205	ODE	6205						
ENCL	TEFC	SN							
	SFA 4.8/2.4								

AC Induction Motor Performance Data

Record # 88679

Typical performance - not guaranteed values

Winding: 75WGW130-R001		Type: 7524M		Enclosure: TEFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)	1.5	Full Load Torque	4.62 LB-FT		
Volts	230/460	Start Configuration	direct on line		
Full Load Amps	4.3/2.15	Breakdown Torque	16.26 LB-FT		
R.P.M.	1710	Pull-up Torque	13.01 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque	14.67 LB-FT	
NEMA Design Code	D KVA Code	J	Starting Current	14.51 A	
Service Factor (S.F.)		1.15	No-load Current	1.15 A	
NEMA Nom. Eff.	81.5 Power Factor	80	Line-line Res. @ 25°C	14.1 Ω	
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	56°C	
S.F. Amps	4.8/2.4		Temp. Rise @ S.F. Load	69°C	
			Locked-rotor Power Factor	65.1	
			Rotor inertia	0.173 lb-ft ²	

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	39	60	72	80	84	86	82
Efficiency	74.5	82.2	83.4	82.5	80.3	77.3	81.2
Speed	1780	1760	1737	1710	1678	1641	1691
Line amperes	1.22	1.44	1.75	2.14	2.6	3.16	2.42


ABB Motors and Mechanical Inc.

WINDING # 75WGW130


Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 1710 RPM 460 V 7524M

TORQUES (LB-FT): PO=16.26 PU=13.01 LR=14.67 LRA=14.51



8/11/2024 ACPERF, record # 88679



CD0005



LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS